







SPECIFICATIONS

Panel Size	27"
Panel Resolution	2560x1440 (WQHD)
Refresh Rate	170Hz
Brightness (nits)	300(Typ.)
Viewing Angle	178°(H) / 178°(V)
Aspect Ratio	16:9
Curvature	1500R
Contrast Ratio	3000:1(Typ.)
Active Display Area (mm)	596.736(H)x335.664(V)
Pixel Pitch (H x V)	0.2331(H)x0.2331(V)
Surface Treatment	Anti-glare
Display Colors	1.07B (8 bits +FRC)
Adobe RGB / DCI-P3 / sRGB	90% / 90% / 115%
Video ports	1x DisplayPort (1.4a) 2x HDMI™ (2.0)
Audio ports	1 x Earphone out
Kensington Lock	Yes
VESA Mounting	75 x 75 mm
Power Input	100~240V, 50~60Hz
Max Weight Capacity	4.55 kg / 6.4 kg 3.85 kg (without stand)
DYNAMIC REFRESH RATE TECHNOLOGY	FreeSync Premium
DCR	100000000:1
HDR Support	HDR Ready
Signal Frequency	90.9-251.1KHz(H) / 48-170Hz(V)
Adjustment (Tilt)	-5° ~ 20°
Dimension (W x H x D)	611.5 x 215.6 x 458.4 mm 611.5 x 99.7 x 364.1 (without stand)
Carton Dimension (W X H X D)	WW carton: 774 x 147 x 461 mm Outer: 789 x 161 x 485 mm
Note	Display Port: 2560x1440 (Up to 170Hz by DP overclocking) HDMI: 2560x1440 (Up to 144Hz) *Adobe RGB, sRGB and DCI-P3 follow CIE1976 standard

FEATURES



Enjoy the most immersive gameplay with 1500R curvature





170 Hz Experience smooth gaming with 170Hz refresh rate, that gives you the upperhand in fast moving games.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.





Provide eye-catching detail through contrast and shadows adjustment.



Night Vision

Smart black tuner to brighten your day by bringing out the fine details in dark areas.



Wide Color Gamut

wide Color Game colors and details will look more realistic and refined, to | Gamut push game immersion to its limits.

CONNECTIONS

Generated 2022-12-28, check for the latest version www.msi.com/datasheet. The information provided in this document is intended for informational purposes only and is subject to change without notice.



- 1. 5-Way Joystick Navigator
- 2. DC Jack
- 3. 2x HDMI[™] (2.0)
- 4. Display Port (1.4a)
- 5. Earphone out