# TRIPP-LITE

1000 Eaton Boulevard Cleveland, OH 44122 United States

## Safe-IT 30W 2-Outlet Surge Protector - 5-15R Outlets, 3 USB Ports, 6 ft. (1.8 m) Cord, 300 Joules, Antimicrobial Protection, White

### MODEL NUMBER: TLP26PD30WCAM



Safely charges and powers up to 5 devices, including laptops and tablets, during important workplace meetings and conferences.

#### Features

#### 2-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home or office workstation or travel use, the TLP26PD30WCAM features a surge suppression rating of 300 joules to defend your sensitive electronic components against power surges and spikes.

#### NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your laptops, projector, printer and other conference-table electronics into two NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. The outlets are spaced widely apart to accept bulky transformers without blocking any outlets or ports.

#### USB Ports Allow Safe and Rapid Charging

Two USB-A ports are available for charging your smartphones, tablets and other USB mobile devices. They share 4.8A of charging power, which is plenty for delivering ample power to demanding devices. A USB-C PD 3.0 port delivers 18W of charging power for laptops and other larger devices. All three ports share 30W maximum.

#### Filtering EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

#### Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT™ TLP26PD30WCAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

#### Compact Round Design Gives You Plenty of Options for Installation and Use

Just four inches in diameter, the TLP26PD30WCAM fits easily into your home or office workspace, providing power and USB charging at your fingertips. Its compact design also makes the surge protector ideal for travel, fitting easily into your backpack, laptop bag or suitcase for use in hotels, conference rooms and cruise ships. The six-foot (1.8-meter) braided power cord connects to an AC wall outlet.

#### Highlights

- 2 NEMA 5-15R outlets are spaced apart to accommodate bulky transformers
- 300 joules protect your valuable electronics against dangerous surges and spikes
- 2 USB-A ports share 4.8A for fast charging of phones, tablets and other mobile devices
- USB-C PD 3.0 charging port delivers 18W of charging power for laptops
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

#### **Package Includes**

- TLP26PD30WCAM 2-Outlet Surge Protector
- Owner's manual



# **Specifications**

OVERVIEW		
UPC Code	037332274915	
Device Compatibility	Laptop; Phone; Tablet	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V	
Input Plug Features	Right Angle	
Input Cord Gauge Type	16 gauge	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	6	
Right-Angle Plug	Yes	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	60 Hz	
Output Receptacles	(2) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(2) Yes	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CON	TROLS	
Diagnostic LED(s)	No	
CHARGING		
Number of Charging Ports	3	
Total Charging Watts	30	
Charging Method	USB	
Charging Port Type	(2) USB A (FEMALE); (1) USB C (FEMALE)	
Charging Ports Details	2 x USB-A (2.4A) charging ports for Phones, laptops, and other devices1 x USB-C 3A PD Chargng Port for fast charging	
Charging Ports / Amps	(1) 3A / 2A / 1.5A; (2) 4.8A	
Overcharge Protection	No	



SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	300	
AC Suppression Response Time	< 1ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
EMI / RFI Filtering	Yes	
Immunity	Conforms to IEE 587/ANSI C62.41	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Material of Construction	Plastic	
Plug Color	White	
Wire Gauge (AWG)	16	
Power Cord Color	White	
Housing Color	White	
Mounting Holes or Slots	No	
Receptacle Color	White	
Shipping Dimensions (hwd / in.)	2.60 x 4.60 x 6.30	
Shipping Dimensions (hwd / cm)	6.60 x 11.68 x 16.00	
Shipping Weight (lbs.)	1.10	
Shipping Weight (kg)	0.50	
Unit Dimensions (hwd / in.)	4.170 x 4.170 x 1.180	
Unit Dimensions (hwd / cm)	10.59 x 10.59 x 3	
Unit Weight (Ibs.)	1.18	
Unit Weight (kg)	0.54	
Rubber Feet	Yes	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	Yes	
GaN Technology	No	



1000 Eaton Boulevard Cleveland, OH 44122 United States

STANDARDS & COMPLIANCE		
Product Certifications	CAN/CSA-C22.2 No. 21 (Canada); ICES (Canada); UL 817	
Product Compliance	FCC Part 15 Class B (USA); RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.