

ASUS BR1102

Reliable laptops for anywhere learning

ASUS BR1102 are Windows 11 Education laptops for K-12 students, featuring a compact 11.6" ruggedized design built for rough handling, extended battery life, TUV-certified display, ASUS Antimicrobial Guard protection, and robust connectivity for uninterrupted learning anywhere.









ASUS ruggedized design

Reliable companion for active K-12

- Compact 11.6" for any backpack
- MIL-STD-810H US military grade durability
- ASUS ruggedized design
- Tamper-resistant exterior
- Reinforced internal components and spill-resistant keyboard
- ASUS Antimicrobial Guard protection
- TÜV-certified display







Expandable dual storage

Anywhere learning without limits

- Windows 11 Education
- Intel® Processor N-Series
- Up to 12-hour battery life
- Easy charging with USB-C on both sides
- Up to WiFi 6, Ethernet, Bluetooth 5° and 4G LTE*



TÜ**V** certified display



Modular design

Easy IT serviceability

- Modular design for technician-friendly maintenance
- Up to 256GB UFS 2.1 storage expandable up to 1TB M.2 PCle 3.0 SSD
- MyASUS support for IT technicians

Performance unleashed

- 180° lay-flat or 360° convertible device compatible with fast-charging ASUS Garaged Stylus SA204H
- Anti-glare (BR1102C) or 178° wide-view (BR1102F) display
- 13MP world facing camera (BR1102F only)

*Optional features

Warranty and Support



3-year global warranty

100% free of charge, with no hidden costs.



Pick up & return service

Enjoy a door-to-door service including pick up , repair, and return.



MyASUS

Contact customer service, view repair status, read product guides and more.

BR1102C SPECIFICATIONS

Model	BR1102C
Operating System	Windows 11 Pro/Windows 11 Home/Windows 11 Pro Education
CPU	Intel® Processor N100
GPU	Intel® Processor N200 Intel® UHD graphics
Memory	Up to 16GB DDR4-3200 MHz Onboard 4GB/8GB/16GB DDR4-3200 MHz
Storage	Up to 256GB UFS2.1 + 1TB PCIe Gen 3 SSD 128GB/256GB UFS2.1 128GB/256GB/512GB/1TB PCIe Gen 3 SSD
Display	11.6" HD (1366 x 768), anti-glare, 220 nits, NTSC 45%
I/O Port	1x USB 3.2 Gen 2 Type-A 1x USB 3.2 Gen 2 Type-C (full function) 1x USB 2.0 Type-C (PD, data transfer) 1x USB 2.0 Type-A 1x HDMI 1.4b 1x 3.5mm Combo Audio Jack 1x RJ45
Camera	720P HD camera
Wireless	Wi-Fi 5 (802.11ac) (Dual band) 1*1 + Bluetooth® 5 Wi-Fi 6 (802.11ax) (Dual band) 2*2 + Bluetooth® 5 4G LTE (eSIM) (optional)
Audio	2x speaker with Dirac audio technology support Array microphone ASUS two-way AI noise-canceling technology Cortana voice-recognition support
Weight	1.37kg
Dimensions (WxDxH)	296.9 x 208.45 x 21.1mm
Battery	50Whr (3-cell lithium-ion polymer)
Security	Fingerprint sensor, webcam shield, Kensington lock slot, TPM 2.0 (optional)
Keyboard	Full size chiclet, 1.35mm key-travel, spill-resistant
NumberPad	N/A
Manageability	ASUS Control Center, ASUS Business Manager, MyASUS
AC Adapter	USB Type-C°, 45 W; Output: 20 V DC, 2.25 A; Input: 100~240 V AC 50/60 Hz universal
LTE	LTE Peak DL 300Mbps (CAT6)/UL 50Mbps (CAT4) (optional)
Sustainability	EPEAT Gold, Energy Star, TCO 9.0, FSC, RoHS
Others	ASUS Antimicrobial Guard

DISCLAIMER: SERVICE PACKAGE MAY DIFFER FROM COUNTRY TO COUNTRY. WE RECOMMEND YOU CHECK WITH YOUR LOCAL DEALERS FOR THE SPECIFICATIONS OF THE PRODUCTS AVAILABLE IN YOUR COUNTRY.

