

Manufacturer Part #	GF63111246
OS	Windows 11 Pro
CPU	Intel® Core™ i7-11800H 8 Core
CPU Speed	2.4 - 4.6GHz
Chipset	HM470
Color	Black
Screen Size	15.6" FHD, IPS-Level 144Hz 45%NTSC
Resolution	1920x1080 (16:9)
GPU	NVIDIA® GeForce RTX™ 3050 Laptop GPU
Video Memory	4G GDDR6
Keyboard	Red keyboard with Anti-Ghost key (99 Key)
Speaker	2x Speakers 2W
Memory	32GB (16GB*2) DDR4 3200MHz
HDD Capacity	1TB NVMe SSD
HDD Interface	NVMe
LAN	Gb LAN
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
Bluetooth	BT 5.1
Card Reader	-
Webcam	720p HD Webcam
USB	3x USB 3.2 Gen1
Type-C Port	1x USB 3.2 Gen1 Type C
Video Port	HDMI 4K @ 30Hz
Audio Port	1 Mic in/ 1 headphone out
AC Power Adaptor	120W
Battery Pack	3 cell , 51Whr Li-Polymer
Dimension	14.13"x9.99"x0.85"
Weight	4.10 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)