

ProductSheet  
**HP E22 G5 FHD Monitor (6N4E8AA)**



## Redefining Focus

Intentionally crafted to deliver crisp visuals, personalized comfort, and true flexibility, the HP E22 G5 FHD Monitor redefines comfort, so there's nothing between you and your best. Stylishly designed with the planet in mind, this display is the perfect fit for both the office and home.



### See it All, Do it All

When the difference is in the details, this 21.5-inch diagonal FHD monitor displays the clarity you need to stay focused on the task at hand. With rich 99% sRGB color depth and IPS technology<sup>[1]</sup>, you'll see clear, vivid colors across wide viewing angles<sup>[2]</sup>.

### Bring Comfort to Work

When doing your best relies on feeling your best, it's easy to find all-day comfort with 4-way adjustability optimized by the step-by-step Ergonomic Setup Guide in HP Display Center<sup>[3]</sup>. Help keep your eyes comfortable with a monitor that comes with flicker-free technology, a 75Hz refresh rate<sup>[1]</sup> and HP Eye Ease, an always-on, built-in low-blue light filter.

### Connect Intuitively

Work how you want with flexible connectivity and settings. Purposefully in reach, the accessible ports make connecting your devices quick and easy, while you effortlessly navigate your on-screen settings with the intuitive joystick OSD button.

## Featuring

### Ergonomic Setup Guide

Achieve all-day comfort when you apply the best practices from the Ergonomic Setup Guide. <sup>[3]</sup>

### Enhanced Viewing Comfort with HP Eye Ease

Always-on, built-in, low-blue light filter that reduces blue light without the yellow color shift now enhanced with a 75Hz refresh rate. <sup>[1]</sup>

### IPS Panel

No matter where you stand, IPS technology ensures image accuracy and consistency across wide, 178-degree horizontal and vertical viewing angles.

### 99% sRGB Color Space

Enjoy what you see on screen with 99% sRGB color space. This display provides ideal color reproduction for vibrant images and videos. <sup>[1]</sup>

### Endless Adjustability

Work effortlessly with 4-way ergonomics that help keep your neck, shoulders, and back comfortable throughout the day. Customize pivot, tilt, 150 mm height adjust, and swivel settings to fit you, your desk, and your needs.

## Specifications

<b>Display size (diagonal)</b>	21.5"
<b>Panel technology</b>	IPS
<b>Aspect ratio</b>	16:9 <sup>[1]</sup>
<b>Native resolution</b>	FHD (1920 x 1080) <sup>[1,2]</sup>
<b>Resolutions supported</b>	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080
<b>Brightness</b>	250 nits <sup>[1]</sup>
<b>Contrast ratio</b>	1000:1 <sup>[1]</sup>
<b>Response time (typical)</b>	5ms GtG (with overdrive) <sup>[1]</sup>
<b>Minimum dimensions (W x D x H)</b>	19.24 x 1.81 x 11.57 in (without hinge); 19.24 x 2.96 x 11.57 in (with hinge) (without stand)
<b>Weight</b>	10.8 lb (with stand)
<b>Display features</b>	On-screen controls; Anti-glare; Height Adjust/Tilt/Swivel/Pivot; HP Eye Ease
<b>Onscreen controls</b>	Management; Information; Exit; Input; Color; Image; Power; Menu; Brightness+
<b>Display colors</b>	Up to 16.7 million colors supported <sup>[3]</sup>
<b>Display scan frequency (horizontal)</b>	30-86 KHz
<b>Display scan frequency (vertical)</b>	50-75 Hz
<b>Camera</b>	No integrated camera
<b>Power</b>	100 - 240 VAC 50/60 Hz
<b>Power consumption</b>	50 W (maximum), 20 W (typical), 0.5 W (standby)
<b>Operating temperature range</b>	5 to 35°C
<b>Operating humidity range</b>	20 to 80% RH
<b>Sustainable impact specifications</b>	Low Halogen; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; Contains ocean-bound recycled plastic; 80% ITE-derived closed loop plastic; At least 25% recycled metal
<b>Certifications and compliances</b>	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CECP; CEL; CEL Grade 1; cTUVus; EAC; ENERGY STAR®; FCC; ISO 9241-307; KC/KCC; Korea MEPS (E-standby); Microsoft WHQL Certification; NOM; PSB; SEPA; TCO Certified; TCO Certified Edge; TUV-S; VCCI; Vietnam MEPS; WEEE; ISC; ICE; UAE; TGM; Ukraine certificates; NRCS; PSE; Hardware low blue light; GS
<b>Ecolabels</b>	EPEAT® Gold
<b>Physical security</b>	Security lock-ready <sup>[12]</sup>
<b>Management Software</b>	HP Display Center; HP Display Manager
<b>UPC number</b>	196786298066
<b>Manufacturer Warranty</b>	3 years limited warranty
<b>What's in the box</b>	Monitor; DisplayPort™ cable; HDMI cable; Warranty card; USB Type-B to A cable; Quick Setup Poster; AC power cord <sup>[11]</sup>

## Top Recommended Displays, Accessories and Services

---

### Personal Systems Commercial Care Pack Services

HP 4y Next Business Day Response Advanced Exchange Small DisplayHardware Support	U0J10E
HP 5y Next Business Day Response Advanced Exchange Small DisplayHardware Support	U0J11E

## Messaging Footnotes

- [1] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- [2] More accurate colors compared to 72% NTSC.
- [3] Ergonomic Setup Guide is available through HP Display Center. Host PC requires Windows 10 or higher. HP Display Center is available on the Microsoft store.

## Technical Specifications Footnotes

- [1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- [2] DisplayPort™ 1.2 or HDMI 1.4 required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 1920 x 1080 at 60 Hz with 8-bit color using one DisplayPort™, HDMI. The video card of the connected PC must be capable of supporting 1920 x 1080 and include one DisplayPort™ or one HDMI outputs to drive the monitor at the preferred mode.
- [3] Number of colors through A-FRC technology.
- [11] Included cables may vary by country.
- [12] Lock sold separately.

**Learn more at**  
[hp.com](https://hp.com)

---

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

DisplayPort™ is a trademark owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. Microsoft, Encarta, MSN, and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

