

SmartRack Industrial Enclosure with Lock - NEMA 4, Wall Mount, Metal Construction, Hinged Back, 28 in. Depth, 9U, Gray

MODEL NUMBER: SRN4G9US











Locking metal enclosure protects your rack-mount equipment against theft, damage, tampering, and excess moisture and debris.

Features

Space-Saving Wall-Mount Enclosure Houses Rack Equipment up to 28 in. Deep

This SmartRack® industrial enclosure is designed to house 9U of 19-inch rack-mount equipment, such as network switches and patch panels. Constructed from steel with a durable gray powder-coated finish, the SRN4G9US has a maximum load capacity of 200 pounds (90.7 kilograms) and is suitable for indoor and outdoor applications.

NEMA 4 Enclosure Designed for Protection Against Harsh Elements

The SRN4G9US protects its contents against the ingress of water (including rain, sleet, snow, splashing water and hose-directed water), solid foreign objects (including falling dirt and windblown dust) and even ice forming on the outside of the enclosure. It is ideal for a multitude of industrial sites, such as factories, construction areas, utility plants, power stations, transportation terminals, distribution hubs, warehouses and other areas where you need to keep sensitive equipment secure, organized and out of the way.

Locks Securely to Help Prevent Theft, Damage and Tampering

The fully welded steel housing locks securely with the included keys to protect its contents against theft, tampering, dust and other contaminants. The enclosure swings away from the wall on a sturdy hinge, allowing easy back-door access to equipment and cabling during installation and maintenance. Data and power cables may be routed through a bottom conduit cutout.

Easy Enclosure and Equipment Installation

This 9U industrial enclosure comes fully assembled and ready to mount to the wall with user-supplied hardware. Front and rear mounting rails adjust independently to accommodate equipment up to 28 inches deep. Hardware for mounting equipment inside the enclosure is included.

Specifications

OVERVIEW

Highlights

- Enclosed, sealed metal housing protects 9U of rack equipment up to 28 in. deep
- NEMA 4 enclosure provides protection against water, ice, snow and other moisture
- Door locks securely with included keys to help prevent damage, tampering or theft
- Enclosure swings away from the wall on hinge for easy back-door access

Package Includes

- SRN4G9US Industrial Enclosure
- (24) 10-32 screws
- (24) M6 washers
- (4) LDPE sheet metal plugs
- (4) M10 foam washers
- (2) Keys
- Owner's manual



UPC Code	037332277145
Device Compatibility	DVR; Network Switch; PDU; Patch Panel; UPS
Rack Type	Small Enclosure
PHYSICAL	
Color	Gray
Material of Construction	Powder Coated Steel
Rack Height	9U
Rack Depth	Mid
Mounting Location	Wall
Factory Preset Rack Depth (in.)	20.00
Factory Preset Rack Depth (cm)	50.8
Factory Preset Rack Depth (mm)	508
Mounting Holes or Slots	Yes
Maximum Device Depth (cm)	71.12
Maximum Device Depth (in.)	28
Maximum Device Depth (mm)	711
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Shipping Form Factor	Factory Assembled
Shipping Dimensions (hwd / in.)	24.25 x 28.00 x 34.00
Shipping Dimensions (hwd / cm)	61.60 x 71.12 x 86.36
Shipping Weight (lbs.)	160.00
Shipping Weight (kg)	72.57
Unit Dimensions (hwd / in.)	18.830 x 24.000 x 30.050
Unit Dimensions (hwd / cm)	47.83 x 60.96 X 76.327
Unit Dimensions (in.)	18.830 x 24.000 x 30.050
Unit Weight (lbs.)	106.8
Unit Weight (kg)	48.44
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Number of Vertical Mounting Rails	4
Mounting Details	Adjustable equipment mounting rail (10-32)
Cable Entry/Exit	Sealed cut-out; compatible gland plates sold separately.



FEATURES & SPECIFICATIONS		
Grounding Details	Cabinet Body	
Tools Necessary	Yes	
Built-in Cable Management	No	
Extra Wide	No	
Locking	Yes	
Lock Type	Кеу	
Pre-Installed Casters	No	
Outdoor Use	Yes	
Gasketed Door	Yes	
STANDARDS & COMPLIANCE		
Protection Rating	NEMA 4	
Product Certifications	CAN/CSA-C22.2 No. 286 (Canada); UL 508A	
Product Compliance	EIA/ECA-310-E; NEMA 4; RoHS; REACH	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	5-year limited warranty	



© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.