

CYBERVIEW 2010

2 MP Smart Outdoor Wifi Wireless



The Gyration Cyberview 2010 is a 2 mp Smart AI Wi-Fi wireless battery camera, suitable for indoor or outdoor use. Support 24 Hrs. event recording; support two-way audio, AI motion detection. Support AI for event monitoring; Instant & accurate alerts; 2.4GHz WiFi connection, support Micro SD card, the maximum capacity can reach 128GB, support cloud storage; Support Android /iOS system mobile devices, remote real-time monitoring. The Cyberview 2010 two-way talk via the CyberView Plus App when someone trigger alert so you'll never miss a video conference. See and talk with your family members or guest of the family from your smartphone anywhere, any time. The built-in microphone and speaker make it easy for you to hear what's happening outdoor or indoor. With CyberView Plus app, you can protect, capture, save and share what's valuable to you.

KEY FEATURES


- High quality image with 2 MP, 1/2.9" CMOS sensor
- 2MP (1920*1080) @ 15 fps Resolution
- Support humanoid detection, vehicle detection, pet capture and package detection (need to open value-added services)
- Supports two-way voice intercom supported; echo eliminated; noise suppressed
- Supports micro SD card (max 128 GB) storage
- Lighting for infrared night vision (with a night vision distance of 7m); 24h around-the-clock monitoring; IR-CUT switching; free of color cast in the daytime; clearer night vision
- Built in rechargeable lithium battery, long life, normal work up to 6 months, standby time up to 12 months
- Supports Android /iOS system mobile devices for remote real-time monitoring
- Smart storage algorithm, small space to accommodate more content, support Micro SD card(up to 128G), cloud storage



Specification		
Sensor	Sensor	1/2.9" color CMOS sensor
	Lens	M12,f: 3.3mm,F2.0, 2MP
	View angle	H(horizontal)95degree; V(vertical)55degree; D(verse)110 degree
	Low illumination	0.01Lux
Audio	Input/output	Two-way voice talk (built-in microphone and speaker)
	Audio compression	AAC
Video	Vedio compression	H.264/H.265
	Light frequency	50Hz, 60Hz
	Frame rate	15fps
	Maximum image	1920*1080P
	Night vision	Choose 8 low power infrared lamps or 2 medium power infrared lamps (850nm wavelength) Optional white light fill
Network	Wireless network	2.4G WIFI(IEEE802.11b/g/n),built-in antenna
	Agreements	TCP/IP、UDP/IP、DHCP、RTMP、MUTP
	Ip address	Dynamic IP address
AI	Smart function	Support humanoid detection, vehicle detection, pet capture and package detection
Alarm	Alarm notification	Mobile APP alarm push, alarm sound warning and equipment white light flashing (optional)
Wake up	Wake up mode	PIR human body induction wake up, remote active wake up

Record	Record method	Alarm triggered, manual recording
	Record	Cloud/Micro SD/Mobile storage
Indication	LED indication	RGB three colors light, indicating power supply / network signal / function status
Battery	Capability	5200mAh
	Detachability	Non detachable
	Usage time	6 months (under the condition of recording 20 10s videos per day)
	Standby time	12 months
	Charging voltage	DV 5V+ -5%/1.5A
	Charging time	10 hours
	Protection mode	IP65 dust proof and waterproof; over current / over discharge / overcharge / short circuit / high and low temperature charging protection
Consumption	Standby power consumption	1.68mW(4V 0.42mA)
	Daytime power consumption	1W((3.8V 264mA)
	Night Power consumption	2.17W((3.8V 571mA)
Port	Power	1个Micro USB port, compatible with type C interface
	SD card	1个Micro SD card (Max support 128GB)
	Button	1pcs reset button, 1pcs switch button
Installation method	Installation method	1 / 4 universal screw hole and magnetic suction
Environment	Dustproof and waterproof	IP65
	Working environment	-10° ~ 45°C /10% ~ 80% (No condensation)
	Stored Environment	-20°C ~ 60° /0% ~ 90%(No condensation)
Specification	Size(LxWxH)	67mm*58mm*89mm (no stand)
	Net Weight	About 212g
	Gross Weight	About 500g
	Material + Technology	PC
	Color	White highlights
Certification	Certificate	CE,FCC,RoHS,WEEE,MSDS,UN38.3

Dimensions (mm)



Shipping Information:

Item	UPC Code	Package Dimensions	Package Weight	Qty/Carton
CyberView 2010	744390953477	4.41 x 5.24 x 2.87 Inch	1 Lbs	40



User Manual