

CYBERVIEW 3000

3 MP Smart Wifi Wireless Doorbell



The Gyration Cyberview 3000 is a 3 mp Smart AI Wi-Fi wireless battery doorbell camera, suitable for outdoor use. Support 24 Hrs. event recording; support two-way audio, AI motion detection. Support PIR motion sensor, Instant & accurate alerts; 2.4GHz WiFi connection, support Micro SD card, the maximum capacity can reach 128GB, support cloud storage; Support Android /iOS system mobile devices, remote real-time monitoring. The Cyberview 3000 initiates a video call via the CyberView Plus App when someone rings your doorbell, so you'll never miss a visitor. See and talk to your visitors from your smartphone anywhere, any time. The built-in microphone and speaker make it easy for you to hear what's happening outside the door. With CyberView Plus app, you can protect, capture, save and share what's valuable to you.

KEY FEATURES

- High quality image with 3 MP, 1/2.8" CMOS sensor
- 3MP (2048*1536) @ 15 fps Resolution
- Supports Motion detection
- Supports two-way audio. Built-in Mic and Speaker
- Supports micro SD card (max 128 GB) storage
- Supports Android /iOS system mobile devices for remote real-time monitoring
- Battery Capacity 5200mAh
- Tamper-proof alert
- IP65





Doorbell Specification		
Camera	Sensor	1/2.8" CMOS
	Focal Length	2.8 mm
	Optical Field of View	156° diagonal, 114° horizontal, 82° vertical
	Minimum Illumination	0.01 lux
Audio	Input	Built-in microphone
	Output	Built-in speaker
	Two-way Audio	Full duplex
	Audio Compressing	AAC
Video	Video Compressing	H.264, H.265
	Lighting Frequency	50 Hz, 60 Hz
	Frame Rate	15 fps
	Maximum Resolution	2048 × 1536
	Light Source for Night Vision	Infrared LED
Network	Wireless Standard	Wi-Fi: 2.4 GHz (IEEE 802.11 b/g/n) FSK: 915 MHz, 868 MHz, 433 MHz
	Protocols Supported	TCP/IP, UDP/IP, DHCP, RTMP, MUDP, FSK
	IP Address Type	Dynamic IP address
Recording	Recording Method	Alarm triggered recording, and manual recording
	Video Storage	Cloud storage, local Micro SD card (up to 128 GB), and mobile phone memory
Function	AI Function	Human detection, vehicle detection, pet detection, package detection, activity zone
	Wake-up Method	PIR body induction wake-up, remote wake-up and button wake-up
	Alarm Notification	Alarm push by mobile app, indicator light flashing and alarm sound warning
	Indicator	RGBY four-color LED
	Mechanical chime and smart speaker compatibility	Mechanical chime, Alexa and Google Home supported

Battery	Capacity	5200 mAh
	Removability	Unremovable
	Working Time	5 months (recording 20 pieces of 10-second video per day)
	Standby Time	1 year
	Charging Voltage	DC: 5 V \pm 5% AC: 8 V ~ 24 V 20 VA
	Charging Time	10 hours (DC)
	Protection	Over-charge, over-discharge, over-current, short circuit and charging protection at high and low temperature
Power Consumption	Standby	3 mW
	Daytime Working	1 W
	Nighttime Working	2.5 W
Interface	Power	Micro USB
	Storage	Micro SD card
	Key	Power key, doorbell key and reset key
Installation	Installation Method	Bracket installation
	Bracket Type	Standard: flat bracket Optional: left and right tilt brackets, up and down tilt brackets
Tamper-proof	Mechanical method	Tools required for doorbell removal
	Electronic method	Alarm sound warning and mobile phone notification in case of illegal doorbell removal (optional)
Environment	Dustproof and Waterproof	IP65
	Operating Temperature	-10 ~ 45
	Storage Temperature	-20 ~ 60 °C
Product Dimension	Dimension	144 mm \times 46 mm \times 31 mm (without bracket)
	Material	PC
	Color	White
Certification	Certification	CE, FCC, RoHS, WEEE, MSDS, UN38.3, UL62368

Wireless Chime Specification		
Power	Power Interface	Micro USB
	Charging Voltage	DC 5 V
Network	Transmission Frequency	915 MHz, 868 MHz, 433 MHz
	Wireless Protocol	FSK
Audio	Number of Tones	Five
	Ringtone Type	Chord
	Loudness	85 dB at 1 meter
Installation	Indoor or Outdoor	Indoor
	Installation Method	Desktop placement
Sync	Multi-device Sync	One doorbell to multiple chimes and one chime to multiple doorbells sync supported
	Package Sync	Doorbell and chime paired in factory when sold in package
Button and Indicator Light	Button	Sync, ringtone selection, volume up, volume down
	Indicator light	Red and blue two-color LED
Environment	Operating Temperature	-10 °C ~ 45 °C
	Storage Temperature	-20 °C ~ 60 °C
Product Dimension	Dimension	65 mm × 65 mm × 20 mm
	Material	PC
	Color	White
Certification	Certification	CE, FCC, RoHS, WEEE

Dimensions (mm)



Shipping Information:

Item	UPC Code	Package Dimensions	Package Weight	Qty/Carton
CyberView 3000	744390953484	3.7 x 2.6 x 6.09 Inch	1.6 Lbs	40



User Manual