

PORTABLE-MONITOR PRO MP161 WORK SMART. PLAY HARD.



# **FEATURES**



#### Ultra Slim & Portable Design

Bring it anywhere you want without any strain or pressure.



### Full HD IPS Panel

Make sure the intensity and purity of colors when gaming.

Support one of the most capable video/audio transmitting



#### Type C Display

Allows you to connect the latest devices more conveniently and with less trouble.

#### Mini HDMI



#### Night Vision

interfaces in the world.

Smart black tuner to brighten your day by bringing out the fine details in dark areas.



## Game Mode

Choose the mode based on the type of game played to experience the best visual effects.

## **SPECIFICATIONS**

REFRESH RATE	60Hz
RESPONSE TIME	4ms (GTG)
BRIGHTNESS (NITS)	250 cd/m2
ASPECT RATIO	16:9
SRGB	53% (CIE 1976)
PIXEL PITCH (H X V)	0.17925(H) x 0.17925(V)
COLOR BIT	6 bits
SPEAKER	2x 1.5W
POWER TYPE	External USB Power (Type C interface)
ADJUSTMENT (TILT)	0° ~ 180°
VIDEO PORTS	1x Mini-HDMI <sup>™</sup> (2.0b) 2x Type-C (DP 1.2a signal with Alt mode & 15W Power Delivery / Power Input)
Dimension (W x H x D)	362.26 x 232.92 x 17.8 mm (14.26 x 9.17 x 0.7 inch)
COMPATIBILITY	PC, Mac, PS5 <sup>™</sup> , PS4 <sup>™</sup> , Xbox, Mobile, Notebook[] * All trademarks and the registered trademarks are the property of their respective owners.
PANEL TYPE	IPS
PANEL RESOLUTION	1920 x 1080 (FHD)
Note	HDMI <sup>™</sup> : 1920 x 1080 (Up to 60Hz) Type-C: 1920 x 1080 (Up to 60Hz) Adaptive-Sync support
PANEL SIZE	15.6"
CONTRAST RATIO	600:1
WEIGHT (NW / GW)	0.75 kg (1.65 lbs) / 2.4 kg (5.29 lbs)
DISPLAY COLORS	262K
SURFACE TREATMENT	Anti-glare
ACTIVE DISPLAY AREA (MM)	344.16(H) x 193.59(V)