



B U S I N E S S & P R O D U C T I V I T Y

Prestige 13 Evo

P R E S T I G E 1 3 E V O A 1 2 M - 0 7 0 U S

Specification

Manufacturer Part #	PRE13EVO12070
OS	Windows 11 Home (MSI recommends Windows 11 Pro for business)
CPU	Intel® Core™ i5-1240P
CPU Speed	1.2 - 4.4Ghz
Chipset	-
Color	Pure White
Screen Size	13.3" FHD+ 16:10 LCD 60Hz, 100% sRGB, IPS-level Display
Resolution	1920x1200 16:10
GPU	Intel® Iris® Xe
Video Memory	-
Keyboard	White backlight keyboard
Speaker	2x Speakers 2W
Memory	16GB LPDDR5-4800MHz
HDD Capacity	512GB NVMe SSD
HDD Interface	NVMe
LAN	-
WLAN	Killer WiFi 6E AX1675 (2x2)
Bluetooth	BT 5.2
Card Reader	Micro SD
Webcam	IR FHD Type [30fps/1080p]
USB	1x USB 3.2 Gen1 (Type-A)
Type-C Port	2x Thunderbolt™ 4 [Support Power delivery, DP 1.4a, USB 4.0]
Video Port	HDMI 2.0 (4K @ 60Hz)
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	65W PD Charging [USB-C]
Battery Pack	4 cell (75Whr) Li-Polymer
Dimension	11.77" x 8.27" x 0.67"
Weight	2.18 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)