

## PERFORMANCE

### Processor

Intel® Core™ i7-12700, 12C (8P + 4E) / 20T, P-core 2.1 / 4.8GHz, E-core 1.6 / 3.6GHz, 25MB

### Graphics

NVIDIA® GeForce RTX™ 3070 8GB GDDR6

### Chipset

Intel® B660 Chipset

### Memory

2x 8GB UDIMM DDR5-4800

### Memory Slots

Four DDR5 UDIMM slots, dual-channel capable

### Max Memory

Up to 128GB DDR5-4800

### Storage

1TB SSD M.2 2280 PCIe® 4.0x4 NVMe®

### Optane™ Memory

None

### Storage Support

Up to five drives, 2x 3.5" HDD + 2x M.2 SSD + 1x open 2.5 HDD Bay

- 3.5" HDD up to 2TB each
- M.2 SSD up to 1TB each

### Card Reader

None

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC897-Q codec

### Power Supply

500W 85%

## DESIGN

### Keyboard

USB Calliope Keyboard, Black, English

### Mouse

USB Calliope Mouse, Black

### Optional Bay

None

### Expansion Slots

- One PCIe® 4.0 x16
- One PCIe® 3.0 x4
- Three M.2 slots (one for WLAN, two for SSD)

### Case Color

Black

### System Lighting

Legion OY Iconic LED + Internal Ambient Lighting

### Chassis

Transparent Cover

### Cooler

Advance Pro Air Cooler

### System Fan

Advance Pro Air Cooling with ARGB (1x Rear + 2x Front)

### Carry Handle

Carry Handle

### Form Factor

Tower (26L)

### Dimensions (WxDxH)

205 x 395.4 x 420 mm (8.1 x 15.57 x 16.54 inches)

### Weight

14 kg (30.86 lbs)

## CONNECTIVITY

### Ethernet

Integrated 100/1000M

### WLAN + Bluetooth®

Wi-Fi® 6, 11ax 2x2 + BT5.1

### Top Ports

- 2x USB 3.2 Gen 1
- 1x headphone (3.5mm)
- 1x microphone (3.5mm)

### Rear Ports

- 1x USB-C® 3.2 Gen 2 (support data transfer and 5V@3A charging)
- 4x USB 2.0
- 2x USB 3.2 Gen 1
- 3x audio connector (3.5mm)
- 1x Lighting switch
- 1x Ethernet (RJ-45)
- 1x power connector

### Optional Rear Ports (configured)

DirectX® 12 on NVIDIA® GeForce RTX™ 3070

## SECURITY & PRIVACY

### Security Chip

Firmware TPM 2.0 integrated in chipset

## SERVICE

### Base Warranty

1-year, Mail-in

### Included Upgrade

3Y Legion Ultimate Support with Onsite (5WSOV25263)

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

## SOFTWARE

### Operating System

Windows® 11 Pro, English

### Bundled Software

None

## MODEL

TopSeller : Yes

Announce Date : 2022-12-22

EAN / UPC / JAN : 196804172477

End of Support : 2027-11-15



intel

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



intel



intel



intel

**Lenovo**

**PSREF**  
Product Specifications  
Reference