

ViewSonic® PROJECTOR **LS751HD**

Key Features

- 2nd generation laser phosphor technology with up to 30,000 hours lifespan
- 5,000 ANSI Lumens offering bright images in any environment
- Up to 300" ultra large screen with lower cost-per-inch
- Installation flexibility: V lens shift, 1.6x optical zoom, H/V keystone
- Versatile application: 360° projection, portrait mode




Product Description

The Luminous Superior series is ViewSonic's lamp-free high brightness lineup for both commercial and educational spaces. The LS751HD adopts industry-leading 2nd generation laser phosphor technology and delivers 5,000 ANSI Lumens while eliminating the use of toxic mercury, reducing the cost and effort of frequent lamp replacement and lowering the total cost of ownership. The lamp-free light source offers enhanced sustainability for a greener environment while delivering up to 300" large images with 1080p high resolution and vivid colors no matter if you're in a boardroom, lecture hall, or public space. The projector boasts high installation flexibility with vertical lens shift, 1.6x optical zoom, easy image adjustment with H/V keystone and 4 corner correction, and diverse applications with 360° projection and portrait mode. The LS751HD also comes with HDMI 2.0b, ensuring access to original 4K quality content with HDR/HLG supported.



- 1. Front IR
- 2. Lens
- 3. HDMI 1.4/HDCP 1.4
- 4. HDMI 2.0/HDCP 2.2
- 5. USB-A (5V/2A, Service)
- 6. Lens
- 7. Audio Out



- 8. RJ45 (LAN Control)
- 9. RS232
- 10. Zoom Ring
- 11. Focus Ring
- 12. LED Indicator
- 13. Keypad
- 14. IR

Visit Us

www.viewsonic.com

SPECIFICATION

Native Resolution:	1920x1080
DMD Type:	DC3
Brightness:	5000 (ANSI Lumens)
Contrast Ratio:	3000000:1
Display Color:	1.07 Billion Colors
Light Source Type:	Laser Phosphor
Light Source Life (hours) with Normal Mode:	20000
Light Source Life (hours) with SuperEco Mode:	30000 (Eco)
Lens:	F=2.5-3.26, f=20.911-32.62mm
Projection Offset:	136%+/-5%
Throw Ratio:	1.4~2.24
Optical Zoom:	1.6X
Digital Zoom:	0.8x-2.0x
Image Size:	30"-300"
Throw Distance:	0.93-14.88m (100"@3.10m)
Keystone:	H:+/-30° , V:+/-30°
Lens Shift V. Range:	+0%, -18%
Audible Noise (Normal):	34dB
Audible Noise (Eco):	31dB
Input Lag:	49.9ms
Resolution Support:	VGA(640 x 480) to 4K UHD(3840 x 2160)
HDTV Compatibility:	480i, 480p, 576i, 576p, 720p, 1080i, 1080p, 4K UHD
Horizontal Frequency:	15K-102KHz
Vertical Scan Rate:	23-120Hz

INPUT

HDMI:	2 (HDMI 2.0/ HDCP 2.2 HDMI 1.4/ HDCP 1.4)
-------	---

OUTPUT

Audio-out (3.5mm):	1
Speaker:	15W x2
USB Type A (Power):	1 (5V/1.5A)

CONTROL

RS232 (DB 9-pin male):	1
RJ45 (LAN control):	1
USB Type A (Services):	1 (share with USB A Output)

OTHERS

Power Supply Voltage:	100-240V+/- 10%, 50/60Hz (AC in)
Power Consumption:	Normal: 245W Standby: <0.5W
Operating Temperature:	0~40°C
Carton:	Brown
Net Weight:	4.5kg
Gross Weight:	6.6kg
Dimensions (WxDxH) with Adjustment Foot:	337x265x131.5mm
Packing Dimensions:	496x195x387mm
OSD Language:	English, French, German, Spanish, Italian, Portuguese, Dutch, Swedish, Finnish, Greek, Norwegian/Danish, Polish, Russian, Simplified_Chinese, Traditional_Chinese, Korean, Arabic, Japanese, Thai, Hungarian, Czechoslovak, Turkish, Farsi, Vietnamese, Indonesian, Romanian, Slovakian, total 27 languages
User Guide Language:	English, S-Chinese, T-Chinese, Indonesian, Finish, French, German, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Swedish, Turkish, Arabic, Czech, Thai, Vietnamese, total 20 languages

STANDARD ACCESSORY

Power Cord:	1
Remote Control:	1
QSG:	Yes
Warranty Card:	Yes (CN Only)

OPTIONAL ACCESSORY

Wall/Ceiling Mount:	PJ-WMK-007
---------------------	------------