



PA511D

Professional Connections | MINGLE BAR

4K image quality with ultra wide FOV

Ultra-wide 124° diagonal field of view to capture more of the room or include additional participants. Supports multiple resolutions, including 4K (Ultra HD) 1080p (Full HD) and 720p (HD) to best support the quality offered by your application and monitor.

Look professional in any light

Provides real-time highly sensitive 3DNR, HDR and AWB technologies with great image optimization in any lighting environment so that you will always look sharp and professional.

AI-powered Auto Framing

Find and frame everyone in the room with the AI auto framing function with AI Gesture recognition.

Intelligent audio pickup

The intelligent audio pickup with AI noise reduction, beamforming and far-field adaptive technologies pick up and reproduce resonant voices from anywhere in the room.

Rich I/O with one-cable connection

One cable connection to get all you need (display, webcam, speakerphone, wired network) to start a meeting easily.

Multiple mounting options

Freedom to mount wherever it works best—table top, wall, tripod or monitor—for the best possible huddle room experience.

Works with most video conferencing applications

Compatible with virtually any video conferencing software apps.


Kensington security slot

Built-in Kensington security slots to help secure the device.





Front View



Rear View

Specifications

Camera

- Maximum Resolution/Frame Rate: 3840x2160/30fps
- Field of View: 124° (D), 115°(H), 79°(V)
- Format: MJPEG, YUY2, and NV12 of UVC 1.0
- Zoom: 4x Digital Zoom
- Image Processing: Auto Framing, Gesture Recognition, 3D Noise Reduction, High Dynamic Range, Auto Lighting Correction, Auto Face Exposure
- Privacy Shutter

Audio

- Microphone: Dual Omnidirectional Microphones
- Microphone Pickup Distance: 4 m/13.12 ft.
- Speaker: 5W with Bass Enhancement
- Audio Processing: AI Noise Reduction, Acoustic Echo Cancellation, Beamforming, Far-field Adaptive, Full Duplex

Interfaces

- 1 x HDMI (4K)
- 1 x USB-A (3.2 Gen 1)
- 1 x USB-C (3.2 Gen 1)
- 1 x RJ45
- 1 x Aux port for recommended expansion microphone (optional)
- 1x LED Indicator
- 2 x K-slot
- Power Connector

Dimensions and Weights

- Dimensions (W x D x H): 295 x 70.4 x 78.7 mm / 11.6 x 2.8 x 3.1 in.
- Weight: 555 g/19.6 oz.

Software - Connect App Add-on Value

- Image Adjustment
- Firmware Update
- Issue Report

*Specifications are subject to change without prior notice.

*Please visit the AVerMedia official website at www.avermedia.com for the latest information.

©2022 by AVerMedia Technologies, Inc. All right reserved. AVerMedia is a registered trademark of AVerMedia Technologies, Inc. All other trademarks belong to their respective companies.

System Requirements

Operating system

Windows 10 or later;

macOS 10.14 or later;

Chrome OS 85.0.4183.131 or later

- Software Compatible: Facebook Messenger, FaceTime, Line, GoToWebinar, Cisco Webex, Microsoft Teams, ZOOM, OBS, StreamLab OBS, Skype, Skype for Business, Slack, Google Meet, Lifesize, Amazon Chime, Whereby (Appear.in)

Hardware System Requirements

- CPU: 3.2 GHz Intel® Core™ i5-4460 processor or better
- RAM: 4 GB or more
- USB: USB 3.1 Gen 1 compatible with USB 2.0 (lower resolution)

What's in the Box

- PA511D
- Quick Start Guide
- USB-C Cable or USB-C to USB-A Cable (Selectable)
- Power Adapter (12V/1.5A)

Optional Accessories

- VESA TV Mount Kit (PN: 112AU360-A53)
- Wall Mount Kit (PN: 112AU360-A4L)
- Expansion Mic (Technica AT9922PC)
- 5m, USB 2.0, Male USB-C to Male USB-A (not support HDMI display)
- 10m, USB 2.0, Male USB-C to Male USB-A (not support HDMI display)

Package Dimensions

- Single Box: 380 x 110 x 130mm (14.96 x 4.33 x 5.12 in.)
- Carton: 55.8 x 38.5 x 29.5cm (21.97 x 15.16 x 11.61 in.)

Shipping Weights

- Single Box : 1060 g (2.34 lbs.)
- Carton: 11.6 Kg (25.57 lbs.) (10 pcs per carton)

EAN	4711289500278
UPC	850036764250