

## PERFORMANCE

### Processor

MediaTek Helio G80 (8C, 2x A75 @2.0GHz + 6x A55 @1.8GHz)

### Graphics

Integrated ARM Mali-G52 MC2 GPU

### Chipset

MediaTek SoC Platform

### Memory

3GB Soldered LPDDR4x

### Storage

32GB eMMC 5.1

### Expandable Memory

microSD Card (up to 128GB, FAT32; 2TB, exFAT)

### Card Reader

microSD Card Slot

### Storage Support

- 32GB eMMC 5.1 on systemboard
- microSD card, supports FAT32 up to 128GB, exFAT up to 2TB

### Camera

Front 2.0MP / Rear 8.0MP

### Microphone

Mono

### Speakers

Dual speaker optimized with Dolby® Atmos®

### Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Coulomb counter
- Hall sensor

### Vibration Motor

Eccentric Rotating Mass (ERM)

### Battery

Integrated 5100mAh (Typ.)

### Max Battery Life

Local video playback: 13 hr

Web browsing: 12 hr

Music playback: 15 hr

### Power Adapter

5V / 2A

## DESIGN

### Display

9" HD (1340x800) IPS 400nits Anti-fingerprint, Touch

### Touchscreen

In-cell, 10-point Multi-touch

### Case Material

Metal (Back Cover)

### Keyboard

None

### Pen

No Support

### Dimensions (WxDxH)

215.43 x 136.76 x 7.99 mm (8.48 x 5.38 x 0.31 inches)

### Weight

Around 344 g (0.76 lbs)

### Case Color

Arctic Grey

## SOFTWARE

### Operating System

Android™ 12 or Later

## CONNECTIVITY

### WLAN + Bluetooth®

11ac 1x1 + BT5.1

### WWAN

None

### NFC

None

### VoiceCall

No

### Standard Ports

- 1x USB-C® 2.0 (support data transfer and Power Delivery 3.0)
- 1x Headphone / microphone combo jack (3.5mm)

### Optional Ports (configured)

1x microSD Card Slot

### Docking

None

## SERVICE

### Base Warranty

1-year, Mail-in with 1-year Battery

## ACCESSORIES

### Bundled Accessories

Clear Case + Film

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

### Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

## MODEL

**Product** : TB310FU

**TopSeller** : No

**Announce Date** : 2022-11-01

**EAN / UPC / JAN** : 196802847902



## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

## Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

## Base Warranty - Included with the system you purchase with default 1-year coverage window.

## Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service\*

\*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



**Lenovo**

**PSREF**  
Product Specifications  
Reference