



SPECIFICATIONS

Panel Size	27" (69cm)
Active Display Area (mm)	597.888(H)x336.312(V)
Curvature	1500R
Panel Type	VA
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.3114(H)x0.3114(V)
Aspect Ratio	16:9
Brightness (nits)	300
Contrast Ratio	3000:1
DCR	100000000:1
Signal Frequency	258.3~274.3 KHz(H) / 96~250 Hz(V)
Refresh Rate	250Hz
Response time	1ms (MPRT)
DYNAMIC REFRESH RATE TECHNOLOGY	FreeSync Premium
HDR Support	HDR Ready
Video ports	1x DP(1.2a) 2x HDMI™ (2.0)
Audio ports	1x Earphone out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	88.7 %/ 89.7% / 113%
Surface Treatment	Anti-glare
Display Colors	10 bits (8 bits + FRC)
Power Type	External Adaptor 20V 2.25A
Power Input	100~240V, 50~60Hz
Adjustment (Tilt)	-5° ~ 20°
Kensington Lock	Yes
Dimension (W x D x H)	611.5 x 225.4 x 457.9 611.5 x 75.9 x 372.8 (without stand)
Carton Dimension (W X D X H)	WW carton: 683 x 157 x 463 mm Outer: 698 x 172 x 488 mm
Frameless Design	Yes
VESA Mounting	100 x 100 mm
Weight (NW / GW)	4.5 kg / 6.3 kg 3.8 kg (without stand)

FEATURES



1500R

Enjoy the most immersive gameplay with 1500R curvature rate.



250Hz High Refresh Rate

Experience smooth gaming with a blazing fast 250Hz refresh rate, that gives you the upperhand in fast moving games.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Night Vision

Smart black tuner to brighten your day by bringing out the fine details in dark areas.



Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.



Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.

Note

Display Port: 1920 x 1080 (Up to 250Hz by DP overclocking)
HDMI™ 2.0: 1920 x 1080 (Up to 240Hz)
Adobe RGB, sRGB and DCI-P3 follow CIE1976 standar

CONNECTIONS



1. 5-way joystick navigator
2. 1x DC Jack
3. 2x HDMI™ (2.0b)
4. 1x Display Port (1.2a)
5. 1x Earphone out
6. 1x Kensington lock