

ProductSheet

HP Color LaserJet Enterprise 6701 dn Printer (58M42A)



Powerfully productive. Extraordinarily efficient.

Transform your workflows with advanced capabilities in a compact footprint. Customizable configurations from print speeds to color panels help to meet the needs of busy workgroups. All while protecting your business against evolving security threats.



Customizable and scalable solutions [8]

Get the functionality you need with unprecedented, flexible configurations built to order. Optimize your device to meet your business needs and your budget.

Fast and seamless digitization

Customize your print experience with cloud-connected HP Workpath apps. Access personalized content and integrate paper and digital workflows.[1]

Everything you expect from an office printer

Advanced workflow solutions makes this fully featured A4 printer the best choice for all your workgroup needs.

Specifications

Print Resolution Technologies	HP ImageREt 3600, Enhanced (600x600 dpi), Fine Lines (1200x1200 dpi), Quickview (300x300 dpi), Pantone Calibrated
Print quality black (best)	Up to 1200 x 1200 dpi
Print quality color (best)	Up to 1200 x 1200 dpi
Print speed black (ISO, A4)	Up to 61 ppm
Print speed black (ISO, letter)	Up to 65 ppm
Print Speed Color (ISO)	Up to 61 ppm
Print speed color (ISO)	Up to 65 ppm
Print speed	Print up to 65 ppm (black) and 65 ppm (color)
Functions	Print
Duplex printing	Automatic
Duty cycle (monthly, A4)	Up to 100,000 pages
Duty cycle (monthly, letter)	Up to 100,000 pages
Printer smart software features	Apple AirPrint™, Mopria-certified, Open Extensibility Platform, FutureSmart Firmware, Instant-on Technology, HP Auto-On/Auto-Off technology, Easy Access USB, Two-Sided Printing, Hardware Integration Pocket, Intuitive 4.3 in (10.9 cm) touchscreen control panel, print multiple pages per sheet (2, 4, 6, 9, 16), collation, watermarks, store print jobs, print preview
Energy savings feature technology	HP Auto-On/Auto-Off Technology; Instant-on Technology; Low-power sleep mode; Power save
Replacement cartridges	W2130A HP 213A Black Original LaserJet Toner Cartridge (~3,500 pages); W2131A HP 213A Cyan Original LaserJet Toner Cartridge (~3,000 pages); W2132A HP 213A Yellow Original LaserJet Toner Cartridge (~3,000 pages); W2133A HP 213A Magenta Original LaserJet Toner Cartridge (~3,000 pages); W2130X HP 213X High Yield Black Original LaserJet Toner Cartridge (~9,000 pages); W2131X HP 213X High Yield Cyan Original LaserJet Toner Cartridge (~6,000 pages); W2132X HP 213X High Yield Yellow Original LaserJet Toner Cartridge (~6,000 pages); W2133X HP 213X High Yield Magenta Original LaserJet Toner Cartridge (~6,000 pages); W2130Y HP 213Y Extra High Yield Black Original LaserJet Toner Cartridge, (~18,000 pages); W2131Y HP 213Y Extra High Yield Cyan Original LaserJet Toner Cartridge (~12,000 pages); W2132Y HP 213Y Extra High Yield Yellow Original LaserJet Toner Cartridge (~12,000 pages); W2133Y HP 213Y Extra High Yield Magenta Original LaserJet Toner Cartridge (~12,000 pages); W2140Z HP 214Z Ultra High Yield Black Original LaserJet Toner Cartridge (~31,000 pages); W2141Z HP 214Z Ultra High Yield Cyan Original LaserJet Toner Cartridge (~26,000 pages); W2142Z HP 214Z Ultra High Yield Yellow Original LaserJet Toner Cartridge (~26,000 pages); W2143Z HP 214Z Ultra High Yield Magenta Original LaserJet Toner Cartridge (~26,000 pages) ^[5]
Supplies feature	TerraJet Cartridge
Connectivity, standard	1 Front USB port; 1 Gigabit Ethernet 10/100/1000T network; 1 SuperSpeed USB 3.0 (device); 1 SuperSpeed USB 3.0 (host)
Connectivity, optional	HP Jetdirect 3100w BLE/NFC/Wireless Accessory 3JN69A; HP Jetdirect LAN Accessory 8FP31A
Network capabilities	Yes, via HP Jetdirect Ethernet embedded print server (standard) which supports: 10Base-T, 100Base-Tx, 1000Base-T; 802.3az (EEE) support on Fast Ethernet and Gig Links; IPsec (standard); 802.11a/b/g/n wireless networking (optional).
Mobile printing capability	Apple AirPrint™; NFC touch-to-print (optional); Mopria™ Certified
Network protocols, supported	Via built-in networking solution: TCP/IP, IPv4, IPv6; Print: TCP-IP port 9100 Direct Mode, LPD (raw queue support only), Web Services Printing, IPP 2.0, Apple AirPrint™, Google Cloud Print; Discovery: SLP, Bonjour, Web Services Discovery; IP Config: IPv4 (BootP, DHCP, AutoIP, Manual, TFTP Config, ARP-Ping), IPv6 (Stateless Link-Local and via Router, Statefull via DHCPv6); Management: SNMPv2/v3, HTTP/HTTPS, Telnet, TFTP Config, FTP FW Download, Syslog; Security: SNMPv3, SSL Cert Management, Firewall, ACL, 802.1x
Software included	No software solutions are included in the Box only on http://hp.com http://123.hp.com , http://support.hp.com ;
Compatible Operating Systems	Windows 11; Windows 10; Windows Client OS; Android; iOS; Mobile OS; macOS 12 Monterey; macOS 11 Big Sur; macOS 10.15 Catalina; Linux; Chrome OS (<i>Citrix Ready Kit Certification - Up to Citrix Server 7.18 for more information see</i>)
Technical features	Automatic 2-sided printing; Bluetooth printing; Cloud-based fleet management; Color touchscreen with apps; ENERGY STAR®; Network printing; Fast first page out; Full ream of paper input; Google Cloud Print; HP Auto-on/Auto-off; TerraJet Toner; Private Print via PIN; Touchscreen; Walk-up USB
Sustainable impact specifications	5% post-consumer recycled plastic; ENERGY STAR® certified; EPEAT® registered
Energy star certified	Yes
Ecolabels	CECP; Blue Angel; IT ECO Declaration; EPEAT® Gold registered; SEPA; KOECO
Blue Angel compliant	Yes, Blue Angel DE-UZ 219—only ensured when using Original HP supplies

Display area (imperial)	3.74 x 2.32 in
Display area (metric)	9.5 x 5.4 cm
Display	4.3 in (10.9 cm) Color Graphic Display (CGD) with touchscreen; rotating (adjustable angle)
Minimum dimensions (W x D x H)	500 x 460 x 415 mm
Minimum dimensions (W x D x H)	19.7 x 18.1 x 16.3 in
Weight	31.14 kg (with supplies)
Weight	68.5 lb (with supplies)
Power consumption	708 watts (Printing/Copying), 47.3 watts (Ready), 1.23 watts (Sleep), 0.08 watts (Auto Off/Manual On), 0.08 watts (Manual Off) (Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.)
Power supply type	Built in 110V or 220 V Power Supply (not dual voltage, power supply varies by part number with option code identifier)
What's in the box	HP Color LaserJet Single-function Printer; HP Black Original LaserJet Toner Cartridge (~7,000 yield), HP Cyan, Magenta and Yellow Original LaserJet Toner Cartridges (~6,000 yield each) (toner cartridges installed); Documentation (Hardware Install Guide); Power cord ^[2]
Manufacturer Warranty	One-year, next-business day, onsite warranty. Warranty and support options vary by product, country and local legal requirements. Go to http://hp.com/support to learn about HP award winning service and support options in your region.

Top Recommended Displays, Accessories and Services

Imaging and Printing Hardware Support Onsite Svc

HP 3 year Next Business Day with DMR Service for Color LaserJet Enterprise 670x	U45RJE
HP 3 year 4 hour 9x5 with DMR Service for Color LaserJet Enterprise 670x	U45RME

Imaging and Printing Commercial Care Pack Services

HP Installation Service with network configuration for Workgroup Printer(1 unit)	U9JT2E
--	--------

Messaging Footnotes

[1] Not all MFPs may be compatible with Workpath apps. To enable HP Workpath, some devices may require optional accessory or firmware to be upgraded. Not all apps may be available in all locations. Subscription may be required. Personalized content and integration functions are applicable to supported HP Workpath apps only.

[8] To learn more about configure to order options, contact your HP or Partner Representative.

Technical Specifications Footnotes

[2] For yield information on the cartridge(s) included with your printer, see <http://www.hp.com/go/toneryield>. Yield values measured in accordance with ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors.

[5] Declared yields based on ISO/IEC 19798 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <https://www.hp.com/go/toneryield>

Learn more at
hp.com

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

