



# **Stereo USB Headset**

Lightweight Over-ear Design, Wired, USB-A Plug, Integrated Controls, Adjustable Microphone, Black

Part No.: 179843

EAN-13: 0766623179843 | UPC: 766623179843

# Over-ear USB Headset - affordable, quality stereo sound for home and office

The Manhattan Stereo USB Headset is your versatile audio tool for common calling applications, such as Skype, Teams or Zoom, across all platforms and operating systems. Whether you're participating in a conference call, listening to a webinar or enjoying your favorite playlist, you'll get reliably clear digital stereo sound quality from generously sized 40 mm drivers every time.

#### Plug and play, easy to use and wired for business

Ready to go out of the box, this USB Headset lets you start talking and listening as soon as you plug its single USB-A connector into your device. It works no matter what operating system your device supports, and you never have to worry about empty batteries since it's USB powered.

#### Comfortable all-day wear

The USB Headset's lightweight, adjustable, padded headband features ultra-soft over-ear cushions that give hours of comfort. You can easily reposition the left-side flexible boom mic for better voice capture and then move it out of the way when you're done making calls.



# manhattan-products.com

#### Convenient in-line controls

Convenient controls located on the USB Stereo Headset's cord make it easy to adjust the volume or mute the mic and speakers individually, all without disrupting the call or your workflow.

#### Features:

- High-quality audio and reliable call clarity, ideal for home and office applications
- Padded over-ear cushions for comfort during long periods of use
- Adjustable, padded headband for secure, relaxed fit
- Flexible, retractable microphone boom for hands-free communication
- Padded microphone to eliminate pop noise
- Integrated volume control with mic- and audio-mute buttons
- Single USB connection for both sound and microphone
- USB connectivity to bypass faulty sound card or audio ports
- Plug and play
- Compatible with all operating systems
- Three-year warranty

### **Specifications:**

#### Standards and Certifications

- USB 2.0
- CE
- FCC
- RoHS

#### Headphones

• Impedance: 32 Ohm

Frequency response: 20 Hz - 20000 Hz
Sensitivity: 103 dB ±3 dB (at 1 mW / 1 Khz)

Driver size: 40 mmOutput: 30 mW (max.)Input voltage: 5 V / 50 mA

#### Microphone

Impedance: 2.2 kOhmType: unidirectional

• Frequency response: 30 Hz - 16 kHz

• Sensitivity: 58 ±3 dB

#### Physical

• Cable length: 1.5 m (5 ft.)

• Total dimensions: 190 x 170 x 87 mm (7.48 x 6.69 x 3.43 in.)



# manhattan-products.com

• Earpad dimensions: 108 x 87 x 40 mm (2.36 x 3.43 x 1.57 in.)

• Weight: 203 g (7.16 oz.)

## System Requirements

Available USB-A port

## **Operating Environment**

• Operation temperature: 0 - 40°C (32 - 104°F)

• Storage temperature: -20 - 60°C (-4 - 140°F)

• Humidity (noncondensing): 0 - 96%

## Package Contents

• Stereo USB Headset

• Quick Instruction Guide







# manhattan-products.com







