

# ExpertBook B3 Flip | B3402

### Achieve more, anytime, anywhere

ASUS ExpertBook B3 Flip is built to embrace the new normal — hybrid working and learning. It's equipped with a 360° hinge, a world-facing camera, and a garaged stylus. ExpertBook B3 Flip also supports 4G LTE for fast and portable connectivity, along with two-way Al-powered noise-cancelation technology. With ExpertBook B3 Flip in your bag, all your worlds are just one twist away.









360° hinge



- 360° flip design with optional garaged MPP 2.0 stylus\* to conquer every using scenario
- An user-facing camera with 13 MP world-facing camera\*
- ASUS exclusive NumberPad 2.0\*



Garaged stylus\*



4G LTE\*



- Up to 11th Gen Intel® Core™ i7 processor with Iris Xe graphic
- Up to 1 TB Storage (easy upgradable M.2 SSD)
- Up to 48 GB DDR4 3200MHz memory (Up to 16 GB on board and 32 GB easy upgradable SO-DIMM)
- WiFi 6 and 4G LTE\* for speedy and stable connectivity everywhere you go
- Two-way Al noise-canceling technology and dual cameras with 3D noisereduction technology for high-quality video conferencing
- Full I/O ports with two Thunderbolt™ 4.0 (PD & DP), HDMI, USB Type-A, RJ45



US military grade



Al noise-canceling technology

### **Outstanding protection**

- ASUS Antibacterial Guard protection on the keyboard, touch pad and palm rest
- TÜV Rheinland certified eyes protection display to protect your eyes from potential harm







ASUS Antibacterial Guard

## **Enterprise-grade durability and security**

- US MIL-STD 810H Military Grade durability for robust protection
- Spill-resistant keyboard (up to 330 cc)
- Reinforced hinge and I/O port bracket
- TPM2.0 / Kensington lock slot / Webcam shield to protect your privacy
- Fingerprint reader / power button combo and single sign on

## Warranty and Support



#### 3-Year global warranty

100% free of charge, with no hidden costs.



#### Pick Up & Return service

Enjoy a door-to-door service including pick up , repair, and return.



#### MyASUS App

Contact customer service, view repair status, read product guides and more.

<sup>\*</sup> Optional specification







SPEC	B3402
Operation System	Windows 11 Pro (ASUS recommends Windows 11 Pro) Windows 11 Home Windows 10 Pro (ASUS recommends Windows 10 Pro) Windows 10 Home Get a FREE upgrade to Windows 11 (when available, see below)
CPU	Intel® Core™ i7-1165G7 processor 2.8 GHz (12MB cache, up to 4.7 GHz, 4 cores) Intel® Core™ i5-1135G7 processor 2.4 GHz (8MB cache, up to 4.2 GHz, 4 cores) Intel® Core™ i3-1115G4 processor 3.0 GHz (6MB cache, up to 4.1 GHz, 2 cores)
GPU	Intel® Iris Xe graphics Intel® UHD graphics
Memory	1 x onboard, 1 x SO-DIMM, up to 48 GB DDR4 3200 MHz Onboard: 4 GB/8 GB/16 GB DDR4 3200 MHz SO-DIMM: 4 GB/8 GB/16 GB/32 GB DDR4 3200 MHz
Storage	1 x M.2 SSD, up to 1 TB PCle® 3.0 SSD 128 GB/256 GB/512 GB M.2 PCle® 3.0 Value SSD 1TB M.2 PCle® 3.0 Performance SSD
Display	14" FHD (1920 x 1080), IPS, 16:9, touch screen, LED backlit, 250 nits, 80% screen-to-body ratio, stylus support 14" FHD (1920 x 1080), IPS, 16:9, touch screen, wide view, LED backlit, 400 nits, 80% screen-to-body ratio, stylus support, 100% sRGB
Stylus	MPP 2.0 garaged stylus (optional)
I/O Port	2 x Thunderbolt™4 Type-C (supports 4K display, USB PD3.0 ), 1 x USB 3.2 Gen1 Type-A, 1 x USB 2.0 Type-A, 1 x HDMI 2.0a, 1 x RJ45, 1 x miscroSD card and nano SIM card combo slot (optional), 1 x 3.5 mm combo audio jack, 1 x Kensington lock slot
Video Camera	720 P HD user-facing camera, Webcam Shield; 13.0 MP world-facing camera (optional)
Wireless	Dual-band 2x2 WiFi 6 (802.11ax) + Bluetooth® 5.0 Dual-band 2x2 WiFi 5 (802.11ac) + Bluetooth® 5.0 Dual-band 1x1 WiFi 5 (802.11ac) + Bluetooth® 5.0 4G LTE embedded with 4 antenna (optional)
Audio	2 x speaker, 2 x multi-array microphone, ASUS two-way Al Noise-Canceling Technology, Cortana voice-recognition support
Weight	1.61 kg
Dimensions (WxDxH)	32.9 x 22.39 x 1.93 cm
Battery	50 Wh, 3-cell, Li-on
Security	Fingerprint sensor (combo power button), TPM 2.0 (optional), Webcam Shield , Kensington lock slot
Keyboard and touchpad	Full-size keyboard with 1.5 mm key travel; backlit (optional); spill-resistant to 330cc*  *Quantity used during testing, with duration of 3 minutes
NumberPad	Optional
Manageability	ASUS Control Center (sold separately), ASUS Business Manager, MyASUS
AC adapter	USB Type-C®, 65 W; Output: 20 V DC, 3.25 A; Input: 100~240 V AC 50/60 Hz universal
Energy efficiency compliance	Energy star, EPEAT Silver

Disclaimer:

1-The Windows 11 upgrade will be delivered to qualifying devices late 2021 into 2022. Timing will vary by device. Certain features require specific hardware (see aka.ms/windows11-spec)

ASUS Expert Series Service Package may differ from country to country. We recommend that you check with your local dealers for the specifications of the products available in your country.

Recommend Accessory







ASUS Mini dock

ZenScreen MB165B