



CONTENT CREATION

CreatorPro Z16 HX Studio

CREATORPRO Z16HXSTUDIO B13VJTO-067US

Specification

Manufacturer Part #	CProZ16P13067
OS	Windows 11 Pro
CPU	Intel® Core™ i9-13950HX
CPU Speed	2.2-5.5 GHz
Chipset	-
Color	Lunar Gray
Screen Size	16" QHD+ (2560*1600), 165Hz DCI-P3 100% Touch panel
Resolution	2560x1600 16:10
GPU	NVIDIA Quadro® RTX A2000
Video Memory	8G GDDR6
Keyboard	Per-key RGB Keyboard (99 key)
Speaker	Dynaudio Speakers 2W*4, DTS
Memory	32GB (16GB*2) DDR5 5200MHz
HDD Capacity	1TB NVMe SSD
HDD Interface	NVMe
Optical Drive Type	dTPM2.0 FIPS 140-2 Compliant
LAN	-
WLAN	Killer WiFi 6E AX1675 (2x2)
Bluetooth	BT 5.2
Card Reader	Full Size SD Express
Webcam	IR FHD Type [30fps/1080p]
USB	1 x USB3.2 Gen2 (Type-A)
Type-C Port	1x Thunderbolt 4™; USB4 w/PD charging; 1 x USB 3.2 Gen 2
Video Port	HDMI -
Audio Port	Mic-in/Headphone-out Combo
AC Power Adaptor	280W
Battery Pack	4 cell (90Whr) Li-Polymer
Dimension	14.13"x10.08"x0.75"
Weight	5.26 lbs
Manufacturer Warranty	3 year Limited warranty (Include 1 Year Global) + 3 year onsite warranty