## Lenovo 500e Yoga Chromebook Gen 4 82W40009US

#### PERFORMANCE

Processor Intel® N100 (4C / 4T, up to 3.4GHz, 6MB)

Graphics Integrated Intel UHD Graphics

Chipset Intel SoC Platform

Memory 4GB Soldered LPDDR5-4800

**Memory Slots** Memory soldered to systemboard, no slots

Max Memory 4GB soldered memory, not upgradable

Storage 32GB eMMC 5.1

Storage Support 32GB eMMC 5.1 on systemboard

Storage Slot eMMC on systemboard, no slots

Card Reader No card reader

Audio Chip High Definition (HD) Audio

Speakers Stereo speakers, 2W x2, optimized with Waves MaxxAudio®, Smart Amplifier (AMP)

Camera Front HD 720p with Privacy Shutter

Microphone 2x, Array (Front)

Battery Integrated 47Wh

Max Battery Life Google power load test: 12 hr

**Power Adapter** 65W USB-C<sup>®</sup> (2-pin)

#### DESIGN

#### Display

12.2" WUXGA (1920x1200) IPS 300nits Glossy / Antifingerprint, 50% NTSC, Corning® Gorilla® Glass, TÜV Low Blue Light, Touch

#### Touchscreen

OGS. 10-point Multi-touch

Kevboard Non-backlit, English

**Case Color** Graphite Grev

Texture

Surface Treatment

**Case Material** PC-ABS + 15% Talc+ TPU (Top), PC-ABS + 15% Talc (Bottom) Pen

Pen Upgradable (Purchase Separately) Dimensions (WxDxH)

287 x 208 x 18.9 mm (11.3 x 8.2 x 0.74 inches) Weight

Starting at 1.32 kg (2.91 lbs)

Others Buttons: power key, volume key

#### SOFTWARE

**Operating System** ChromeOS **Bundled Software** 

None

#### CONNECTIVITY

#### Ethernet

No Onboard Ethernet WLAN + Bluetooth®

Intel Wi-Fi<sup>®</sup> 6E AX211, 11ax 2x2 + BT5.1

#### **WWAN** None

SIM Card

#### None

Standard Ports

- 2x USB 3.2 Gen 1
- 1x USB-C 3.2 Gen 2 (support data transfer, Power Delivery and DisplayPort<sup>™</sup>)
- 1x HDMI® 1.4
- 1x Headphone / microphone combo jack (3.5mm)

#### **SECURITY & PRIVACY**

#### Security Chip

Google Security Chip H1

### **Fingerprint Reader**

None

Lenovo

PSRFF Product Specifications Reference

#### **Physical Locks**

Kensington® NanoSaver® lock Slot

**Other Security** Camera privacy shutter

#### MANAGEABILITY

#### SERVICE

**Base Warranty** 1-vear. Mail-in

Included Upgrade

None

#### ACCESSORIES

**Bundled Accessories** None

#### CERTIFICATIONS

#### **Green Certifications**

- EPEAT<sup>™</sup> Gold Registered
- ENERGY STAR® 8.0
- ErP Lot 6
- FrPlot 26
- TCO Certified 9.0
- RoHS compliant

#### **Other Certifications**

- TÜV Rheinland<sup>®</sup> Low Blue Light (Hardware Solution)
- ASTM F963 test passed

#### **Mil-Spec Test**

MIL-STD-810H military test passed

#### MODEL

TopSeller	: Yes	Announce Date	: 2023-04-11
EAN / UPC / JAN	: 196804128160	End of Support	: N/A



· Lenovo reserves the right to change specifications or other product information without notice.

· Battery life is an estimated maximum. Actual battery life may vary by hardware or system settings, active applications, battery conditioning, etc.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the

time of sale of the product. For more information, go to: https://www.calrecycle.ca.gov/Electronics/Consumer

## Premium Care - Advanced Support from Real People. Real Fast.

# 2

REAL PERSON

Choose how you want to reach us through the phone, chat or email - our expert technicians will take care of you.

## HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



## REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

### **PC HEALTH CHECK**



Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

Pick Up & Return Courier

Technician Installed Customer

Onsite Support

- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



## **Recommended Services**

GOOD

3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0Q81869)

For a full list of accessories and services, please visit: https://smartfind.Lenovo.com

