

## Key Features


- 4,500 ANSI Lumens, offering clear images in any environment
- Up to 300" ultra large screen with lower cost-per-inch
- Easy and flexible connection: dual HDMI ports, USB Type-A port
- Vivid colors with
  ViewSonic's SuperColor™
  Technology
- Convenient software updates for projectors via USB connection



## Product **Description**

The PA700W is ViewSonic's high brightness WXGA business/education projector. With 4,500 ANSI Lumens of highbrightness, the projector offers clear images of up-to-300" large screen in meeting rooms, classrooms, or anyother bright environment. The dual HDMI ports allow you to flexibly connect to multiple devices, easily switchingbetween content sources. The USB Type-A port can supply power to HDMI wireless dongles, making wireless contentstreaming more convenient. The projector also allows software updates via USB cable connection with simply yourlaptops, skipping trips to service centers.





## SPECIFICATION

SPECIFICATION		OTHERS			
Native Resolution:	1280x800	Power Supply	100-240V+/- 10%,	0-240V+/- 10%, 50/60Hz C in)	
Brightness:	4500 (ANSI Lumens)	Voltage:	(AC in)		
Contrast Ratio with SuperEco Mode:	12500:1	Power Consumption:	Normal: 295W Standby: <0.5W		
Display Color:	1.07 Billion Colours	Operating Temperature:	0~40°C		
Light Source Type:	240W UHP Lamp	Carton:	Brown		
Light Source Life (hours) with Normal Mode:	4000	Net Weight:	2.70kg		
Light Source Life (hours) with SuperEco Mode:	12000	Gross Weight:	3.80Kg		
Lens:	F=2.41-2.53, f=21.85-24mm	Dimensions (WxDxH) with	309x234x115mm	309x234x115mm	
Projection Offset:	112.4%+/-5%	Adjustment Foot:			
Throw Ratio:	1.544-1.72	Packing	400x337x168mm		
Optical Zoom:	1.1x	Dimensions: 400X337X108111			
Digital Zoom:	0.8x-2.0x	OSD	English, German, French, Swedish, Spanish, Portuguese, Polish, Dutch, T. Chines Finnish, Korean, Russian, Hungarian, Czech, Arabic, Thai, Turkish, Vietnamese, I Italian, Total 22 languages		
Image Size:	30"-300"	Language:			
Throw Distance:	1.00m-11.11m (100"@3.33m)	User Guide Language:	English, S-Chinese, T-Chinese, Finnish,French,German,Italian,Japanese,Korean,Polish,Portuguese,Russian,Spar Total 15 languages		
Keystone:	+/- 40° (V)	STANDARD A	ACCESSORY		
Audible Noise (Normal):	34dB	Power Cord:		1	
Audible Noise (Eco):	25dB	VGA Cable:		1	
Input Lag:	33.2ms	Remote Control:		1	
Resolution Support:	VGA(640 x 480) to FullHD(1920 x 1080)	QSG:		Yes	
	480i, 480p, 576i, 576p, 720p, 1080i,	30i, Air Filter: Warranty Card:		Yes (CN Only)	
HDTV Compatibility:	1080р			Yes (CN Only)	
Video Compatibility:	NTSC, PAL, SECAM	OPTIONAL ACCESSORY			
Horizontal Frequency:	15K-102KHz	Lamp/Light Source:		RLC-128	
Vertical Scan Rate:	23-120Hz	Air Filter:		RSPL	
INPUT		Wall/Ceiling Mount:		PJ-WMK-007	
Computer in (share with component):	1	Carry Bag:		PJ-CASE-008	
HDMI:	2 (HDMI 1.4/ HDCP 1.4)				
Audio-in (3.5mm):	1				
OUTPUT					
Monitor out:	1				
Audio-out (3.5mm):	1				
Speaker:	3W				
USB Type A (Power):	1 (5V/1.5A)				
CONTROL					
RS232 (DB 9-pin male):	1				
USB Type A (Services):	1 (share with USB A Output)				