

## **COOLER MASTER TEMPEST GP27Q**

## THE COMPETITIVE WORK/PLAY CHOICE



#### **FEATURES**

#### • YOUR PLAY-WORK-MOVIE SOLUTION

Tempest GP27Q is a high-powered staple tool in your daily life for gaming, working ,entertaining and creators . It delivers superior images and accurate colors with a more responsive overall experience. Access game mode by turning on Adaptive sync for smooth and faultless visuals.

#### AHEAD OF YOUR COMPETITION

By having up to 165Hz ultra-high refresh rate, 1ms response time, winning is within your reach whilst working or movie sessions will have less motion blur and smearing.

#### STUNNING IMAGE QUALITY

According new Quantum Dot technology, it can deliver lively and outstanding colors with Ultra wide color gamut of Adobe RGB 99% and DCI-P3 98%. Mini LED technology will deliver deep black and ultimate contrast of HDR performance to enjoy better vision world.

#### WIN IN COMFORT

Deliver smooth and comfort working experience with delta E < 2 and full spec high adjustment stand .

The Tempest GP27Q is designed for everyone and offers outstanding value and competency with Mini LED WQHD 165Hz that empowers your work/play experience with an Quantum Dot wide gamut technology wide gamut of Adobe RGB 99% and DCI-P3 98%.

We offer gamers and creatives a quality time for gaming, entertainment and powerful work tool, all in an affordable stylish package.

munu		<i>.</i>						
Product Name			Tempest GP27Q					
Product Number			CMI-GP27-FQS					
Curve / Ratio / Screen Size			Flat / 16:9 / 27"					
Panel			Ultra-Speed IPS 1.07B colors w/Quantum Dot					
Resolution			WQHD 2560*1440					
Frame Rate			165 Hz					
Contrast Ratio			1000:1					
Viewing Angle (H/V)			178°/178°					
Brightness ( SDR ) Brightness ( HDR Peak )			600 nits 1200 nits					
DisplayHDR1000			Compatible					
Color Gamut			Adobe RGB 99% / DCI-P3 98%					
I/O (Input/Output)			DP*1 +HDMI2.0*2 +TypeC (90W PD+DP ALT+USB data)*1 +USB3.2 TypeB*1+TypeA*2 + speaker 3W*2					
Local dimming			Mini LED 576 zone					
VRR Technology			Adaptive Sync FreeSync Range: Yes G-Sync Range: Yes					
Response Time			1ms					
Eye Protection			Low Blue Light					
Anti-flicker			Yes					
Overdrive Technology			Yes					
Power Consumption			39.5W*					
Lighting			Rear cover lighting					
VESA			100*100mm					
Adjustability			Height Adjustment: 0-110mm Tilt: -5°-20° Swivel: ±15° Pivot: 0°±90°					
	ure a screen br			Onits without				
audio/USB/Card reader conr Net weight (Kg)			5.1kg					
Gross weight (Kg)			9.2kg					
	e (L x W x H)		830*215*500mm					
Warrant	y		3 years					
Size	Container	W/	Pallet	Carton/ Pallet	W/O Pallet			
27"	20GP		240	20pcs / pallet	280			
	1000		560	, , , , , , , , , , , , , , , , , , , ,	700			

40HQ

560

700



# **COOLER MASTER TEMPEST GP27Q**

## **GLOBAL POWER CORD**

Model	Part Number	中文說明	EAN	UPC	China
	CMI-GP27-FQS-US	GP27-FQS美規電源線	4719512126882	884102099205	—
	CMI-GP27-FQS-EK	GP27-FQS歐規英規電源線	4719512126899	884102099212	—
	CMI-GP27-FQS-AP	GP27-FQS 澳規電源線	4719512126905	884102099229	—
GP27-FQS	CMI-GP27-FQS	GP27-FQS 不附電源線	4719512126912	884102099236	—
	CMI-GP27-FQS-ST	GP27-FQS 瑞士規電源線	4719512127629	884102099946	—
	CMI-GP27-FQS-BR	GP27-FQS巴西規電源線	4719512135198	884102107511	—
	CMI-GP27-FQS-TW	GP27-FQS 台灣規電源線	4719512135594	884102107917	—