



Make It Yours.

# COOLER MASTER TEMPEST GP27U

## THE COMPETITIVE WORK/PLAY CHOICE



### FEATURES

#### • YOUR PLAY-WORK-MOVIE SOLUTION

Tempest GP27U is a high-powered staple tool in your daily life for gaming, working ,entertaining and creators . It delivers superior images and accurate colors with a more responsive overall experience. Access game mode by turning on Adaptive sync for smooth and faultless visuals.

#### • AHEAD OF YOUR COMPETITION

By having up to 160Hz ultra-high refresh rate, 1ms response time , winning is within your reach whilst working or movie sessions will have less motion blur and smearing.

#### • STUNNING IMAGE QUALITY

According new Quantum Dot technology , it can deliver lively and outstanding colors with Ultra wide color gamut of Adobe RGB 99% and DCI-P3 98% . Mini LED technology will deliver deep black and ultimate contrast of HDR performance to enjoy better vision world

#### • WIN IN COMFORT

Deliver smooth and comfort working experience with delta E < 2 and full spec high adjustment stand .

The Tempest GP27U is designed for everyone and offers outstanding value and competency with Mini LED UHD 160Hz that empowers your work/play experience with an Quantum Dot wide gamut technology wide gamut of Adobe RGB 99% and DCI-P3 98% .

We offer gamers and creatives a quality time for gaming, entertainment and powerful work tool, all in an affordable stylish package.

### SPECIFICATIONS & PACKING INFORMATION

Product Name	Tempest GP27U
Product Number	CMI-GP27-FUS
Curve / Ratio / Screen Size	Flat / 16:9 / 27"
Panel	Ultra-Speed IPS 1.07B colors w/Quantum Dot
Resolution	UHD 3840 * 2160
Frame Rate	160 Hz
Contrast Ratio	1000:1
Viewing Angle (H/V)	178°/178°
Brightness ( SDR ) Brightness ( HDR Peak )	600 nits 1200 nits
DisplayHDR1000	Compatible
Color Gamut	Adobe RGB 99% / DCI-P3 98%
I/O (Input/Output)	DP*1 +HDMI2.1(48Gbps)*2 +TypeC (90W PD+DP ALT+USB data)*1 +TypeB*1+USB3.2 TypeA*2 + speaker 3W*2
Local dimming	MiniLED 576 zone
VRR Technology	Adaptive Sync FreeSync Range: Yes G-Sync Range: Yes
Response Time	1ms
Eye Protection	Low Blue Light
Overdrive Technology	Yes
Lighting	Rear cover lighting
Delta E <2	Yes
FW update	Yes(USB)
Power consumption	47.7W*
VESA	100*100mm
Adjustability	Height Adjustment: 0-110mm Tilt: -5°-20° Swivel: ±15° Pivot: 0°±90°

\* Measure a screen brightness of 200nits without audio/USB/Card reader connection.

Net weight (Kg)	5.1kg
Gross weight (Kg)	9.1kg
Package (L x W x H)	830*215*500mm
Warranty	3 years

Size	Container	W/ Pallet	Carton/ Pallet	W/O Pallet
27"	20GP	240	20pcs / pallet	280
	40HQ	560		700



Make It Yours.

# COOLER MASTER TEMPEST GP27U

## GLOBAL POWER CORD

Model	Part Number	中文說明	EAN	UPC	China
GP27-FUS	CMI-GP27-FUS-US	GP27-FUS美規電源線	4719512126929	884102099243	—
	CMI-GP27-FUS-EK	GP27-FUS 歐規英規電源線	4719512126936	884102099250	—
	CMI-GP27-FUS-AP	GP27-FUS 澳規電源線	4719512126943	884102099267	—
	CMI-GP27-FUS	GP27-FUS 不附電源線	4719512126950	884102099274	—
	CMI-GP27-FUS-ST	GP27-FUS 瑞士規電源線	4719512127612	884102099939	—
	CMI-GP27-FUS-CN	GP27-FUS中國電源線	—	—	6928968316893
	CMI-GP27-FUS-BR	GP27-FUS巴西電源線	4719512135204	884102107528	—
	CMI-GP27-FUS-TW	GP27-FUS 台灣規電源線	4719512135587	884102107900	—