## **MSí**®

## LAPTOPS Stealth 16 Studio STEALTH 16 STUDIO A13VG-208US

## Specification

Manufacturer Part #	STEALTH1613208
OS	Windows 11 Pro
CPU	Intel® Core™ i7-13700H
CPU Speed	3.7-5.0 GHz
Chipset	
Color	Star Blue
Screen Size	16" QHD+ Wide View Angle 240Hz Thin Bezel 100% DCI-P3
Resolution	2560x1600 16:10
GPU	NVIDIA® GeForce RTX <sup>™</sup> 4070 Laptop GPU Up to 1980MHz Boost Clock 105W Maximum Graphics Power with Dynamic Boost. *May vary by scenario
Video Memory	8G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (99 Key)
Speaker	Sound by Dynaudio, 2x2W Speaker, 4x2W Duo Wave Woofer
Memory	64GB (32GB*2) DDR5 5200MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
LAN	Killer E3100G
WLAN	Intel Wi-Fi 6 AX211(2*2 ax)
Bluetooth	BT 5.3
Card Reader	Micro SD 4.0
Webcam	1080p FHD with shutter
USB	1x USB 3.2 Gen2
Type-C Port	1x Thunderbolt™ 4 w/DP&PD 1x USB 3.2 Gen 2/DP
Video Port	HDMI v2.1,
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	240 W *2
Battery Pack	4 cell (99.9Whr) Li-Polymer
Dimension	14"x 10.22"x 0.85"
Weight	4.19 lbs
Manufacturer Warranty	3 year on site warranty+ADP