

## PERFORMANCE

### Processor

Intel® Core™ i7-1370P, 14C (6P + 8E) / 20T, P-core 1.9 / 5.2GHz, E-core 1.4 / 3.9GHz, 24MB

### Graphics

Integrated Intel Iris® Xe Graphics Functions as UHD Graphics

### Chipset

Intel SoC Platform

### Memory

16GB Soldered DDR5-5600 Non-ECC

### Memory Slots

Models with DDR5 memory: one memory soldered to systemboard, one DDR5 SO-DIMM slot, dual-channel capable

### Max Memory

Models with DDR5 memory: up to 48GB (16GB soldered + 32GB SO-DIMM)

### Storage

512GB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

### Storage Support

One drive, up to 2TB M.2 2280 SSD

### Storage Slot

One M.2 2280 PCIe 4.0 x4 slot

### Card Reader

No card reader

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 2W x2, Dolby® Audio™

### Camera

5.0MP + IR Discrete with Privacy Shutter and Human Presence Detection

### Microphone

2x, Array

### Battery

Integrated 86Wh

### Power Adapter

135W USB-C® Slim (3-pin)

## DESIGN

### Display

16" WUXGA (1920x1200) IPS 300nits Anti-glare, 45% NTSC

### Keyboard

Backlit, English

### Case Color

Villi Black

### Case Material

PC + 20% CF + 50% GF (Top), PPS (Bottom)

### Dimensions (WxDxH)

361.98 x 255.5 x 20.5 mm (14.25 x 10.06 x 0.81 inches)

### Weight

Starting at 1.70 kg (3.77 lbs)

## SOFTWARE

### Operating System

Windows® 11 Pro, English

## CONNECTIVITY

### Ethernet

100/1000M (RJ-45)

### WLAN + Bluetooth®

Intel Wi-Fi® 6E AX211, 11ax 2x2 + BT5.1

### WWAN

WWAN Upgradable to 4G

### Standard Ports

- 2x USB 3.2 Gen 1 (one Always On)
- 2x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 2.0)
- 1x HDMI®, up to 4K/60Hz
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Security keyhole

### Optional Ports (configured)

1x Nano-SIM Card Slot

### Docking

Various docking solutions supported via Thunderbolt or USB-C.

For more compatible docking solutions, please visit .

[Docking for ThinkPad® P16s Gen 2 \(Intel\)](#)

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0 Enabled

### Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

### Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

### Other Security

- Ultrasonic Human Presence Detection for IR camera
- Camera privacy shutter
- Ultrasonic Human Presence Detection for IR camera
- IR camera for Windows® Hello
- Bottom cover tamper detection

## MANAGEABILITY

### System Management

Intel® vPro® Enterprise

## SERVICE

### Base Warranty

3-year, Courier or Carry-in

### Included Upgrade

3Y Sealed Battery Add On (5WS1H31713), 3Y Premier Support Upgrade from 3Y Courier/CCI (5WS1H31725)

## CERTIFICATIONS

### Green Certifications

- EPEAT™ Gold Registered
- ENERGY STAR® 8.0
- TCO Certified 9.0
- RoHS compliant

### Mil-Spec Test

MIL-STD-810H military test passed

### ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

## MODEL

TopSeller : Yes

Announce Date : 2023-04-25

EAN / UPC / JAN : 196804637181

End of Support : 2029-11-25



## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

The ThinkPad Hybrid USB-C with USB-A Dock expands the capabilities of most any laptop, new or old, making it perfect for enterprise customers with mixed-PC or shared-desk environments. Featuring enterprise-class manag...

## Recommended Services

BEST	5Y Lenovo Protect (Premier Support + ADP + KYD + International Service Entitlement) For Embedded MTM (5PS1K54547)
BETTER	4Y Lenovo Support (Premier Support + KYD + International Service Entitlement) For Embedded MTM (5PS1K54545)
GOOD	3Y Lenovo Protect (ADP + KYD + International Service Entitlement) For Embedded MTM (5PS1K54544)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference