

## PERFORMANCE

### Processor

Intel® Core™ i7-13700, 16C (8P + 8E) / 24T, Max Turbo up to 5.2GHz, P-core 2.1 / 5.1GHz, E-core 1.5 / 4.1GHz, 30MB

### Processor Sockets

1x FCLGA1700

### Integrated Graphics

Integrated Intel UHD Graphics 770

### Discrete Graphics

1x NVIDIA® RTX A2000 12GB

### Chipset

Intel W680 Chipset

### Memory

1x 32GB UDIMM DDR5-4800 Non-ECC

### Memory Slots

4 DDR5 DIMM slots, 2 channels capable

### Max Memory<sup>(7)</sup>

Up to 128GB (4x 32GB DDR5 UDIMM)

### M.2 SSD RAID Controller

Integrated NVMe® Controller

### M.2 SSD Drive

1x 1TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe Opal

### HDD Controller

Onboard Intel RSTe SATA RAID

### Storage Support<sup>(8)</sup>

Up to 5 drives (4x HDD + 1x M.2 SSD) or 6 drives (3x HDD + 3x M.2 SSD)

- 3.5" HDD up to 6TB each
- 2.5" HDD up to 1TB each
- M.2 SSD up to 4TB or 2TB each (see Storage Type)

### Audio Chip

High Definition (HD) Audio, Realtek® ALC897Q-CG codec

### Power Supply

750W Platinum Fixed

## DESIGN

### Keyboard

USB Traditional Keyboard, Black, English

### Mouse

USB Calliope Mouse, Black

### Expansion Slots

- One PCIe 4.0 x16
- One PCIe 4.0 x16 (x4 lanes)
- Two PCIe 3.0 x1

### M.2 Slots

- Up to 3x M.2 SSD:
  - 2 via onboard slot, can't be available when 4th HDD is selected
  - 1 via Single M.2 to PCIe adapter
- One M.2 slot (for WLAN)

### Bays

Up to four disk bays:

- Bay 1 supports one 3.5" / 2.5" HDD, standard
- Bay 2 supports one 3.5" / 2.5" HDD, optional
- Bay 3 supports one 3.5" / 2.5" HDD, optional
- Bay 4 supports one 3.5" / 2.5" HDD, optional
- Front Access HDD Bay supports one 3.5" / 2.5" HDD, optional, occupies Bay 3 location

### Dimensions (WxDxH)<sup>(9)</sup>

180 x 370 x 415 mm (7.09 x 14.57 x 16.34 inches)

### Weight<sup>(10)</sup>

13.6 kg (29.9 lbs, maximum configuration)

## CONNECTIVITY

### Onboard Ethernet

Intel I219-LM, 1x GbE RJ-45

### Card Reader

SD Card Reader

### Front Ports

- 2x USB 3.2 Gen 1
- 2x USB 3.2 Gen 2
- 1x USB-C® 3.2 Gen 2
- 1x headphone / microphone combo jack (3.5mm)
- 1x microphone (3.5mm)

### Rear Ports<sup>(11)</sup>

- 1x HDMI® 2.1 TMDS
- 2x DisplayPort™ 1.4
- 4x USB 3.2 Gen 1 (one supports Smart Power On)
- 1x Ethernet (RJ-45)
- 1x line-out (3.5mm)

### Optional Rear Ports (configured)

1x DP (Flex IO)

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0, TCG certified

### Physical Locks

- Kensington® Security Slot™, 3 x 7 mm
- Padlock Loop

### Chassis Intrusion Switch

Chassis Intrusion Switch

## MANAGEABILITY

### System Management

Intel® vPro® Enterprise with Intel AMT 16

## SERVICE

### Base Warranty

3-year, Onsite

### Included Upgrade

3Y Premier Support Upgrade from 3Y Onsite

## CERTIFICATIONS

### Green Certifications<sup>(12)</sup>

- EPEAT™ Gold Registered
- ENERGY STAR® 8.0
- ErP Lot 3
- TCO Certified 9.0
- RoHS compliant

### ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

## SOFTWARE

### Operating System

Windows® 11 Pro, English

## MODEL

**TopSeller** : Yes **Announce Date** : 2023-04-25

**EAN / UPC / JAN** : 196804913902 **End of Support** : 2031-05-25



To see more note information, please link to [https://psref.lenovo.com/Detail/ThinkStation\\_P3\\_Tower?M=30GS0037US](https://psref.lenovo.com/Detail/ThinkStation_P3_Tower?M=30GS0037US).

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

## Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L39058)
BETTER	3Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L39322)
GOOD	4Y Premier Support upgrade from 3Y Premier Support (5WS0W86700)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference