



HP Z2 Tower G9 Workstation (87D62UT)



Overview

Pro-power. Today and tomorrow

Experience a whole new level of performance for your professional workflow. The Z2 Tower is engineered to seamlessly run multi-threaded apps for fast rendering, simulation, and now real-time ray tracing. And when your demands change, you have impressive expandability to upgrade.

Your new benchmark for entry workstation power

Designed for zero throttling so you can render, simulate, and real-time ray trace without overheating or lags.

ISV Certified

Work with confidence knowing your PC is certified with leading software applications to ensure peak performance[3]

Built to expand. Power to grow

With room to expand and tool-less access, you can easily upgrade and add components as your needs evolve.

Features

Windows 11

Work anywhere without compromising on performance or security with Windows 11 powered by HP's collaboration and connectivity technology.

Intel® Core™ i7 processor

Run several CPU-heavy programs simultaneously without sacrificing performance with an Intel® Core™ i7 processor.^[4]

Security is your top priority

The HP Wolf Pro Security Edition provides preconfigured enterprise-level PC protection for small and medium sized businesses.

Smaller, Functional Design

The stunning new design features front and rear ledges, so you can easily move your system from location to location.

[3] Third party software sold separately.

[4] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

Specifications

Operating system	Windows 11 Pro ^[1]
Processor family	13th Generation Intel® Core™ i7 processor
Processor	Intel® Core™ i7-13700 (up to 5.2 GHz with Intel® Turbo Boost Technology, 30 MB L3 cache, 16 cores, 24 threads) ^[6,7]
Memory	16 GB DDR5-4800 MHz RAM (1 x 16 GB)
Memory Slots	4 DIMM
Internal Storage	512 GB HP Z Turbo Drive PCIe® NVMe™ TLC M.2 SSD
Internal drive bays	One 2.5" HDD; Two 3.5" HDD; Three M.2 NVME 2280 SSD
External drive bays	One slim ODD; One 5.25" ODD
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics 770
Compatible displays	All HP Z Displays and HP DreamColor Displays are supported. For more information see www.hp.com/go/zdisplays
Audio	Realtek ALC3205-VA2-CG, 2.0W internal mono speaker
Minimum dimensions (W x D x H)	35.6 x 16.9 x 38.5 cm (Standard tower orientation.)
Minimum dimensions (W x D x H)	14 x 6.7 x 15.2 in (Standard tower orientation.)
Weight	Starting at 7.2 kg (Exact weight depends on configuration.)
Weight	Starting at 16 lb (Exact weight depends on configuration.)
Keyboard	HP Wired Desktop 320K Keyboard
Pointing device	HP Wired 320M Mouse
Ports	4 SuperSpeed USB Type-A 10Gbps signaling rate (1 charging); 1 universal audio jack
Expansion slots	1 PCIe 3 x4 (x16 connector); 1 PCIe 3 x4 (x4 connector); 1 PCIe 3 x1 (x4 connector); 1 PCIe 5 x16 (x16 connector); 1 M.2 2230 PCIe 3 X1 for WLAN (1 M.2 2230 slot for WLAN and 3 M.2 2280 slots for storage)
Ports	1 audio-in; 1 audio-out; 1 RJ-45; 2 DisplayPort™ 1.4; 2 SuperSpeed USB Type-A 10Gbps signaling rate; 1 SuperSpeed USB Type-A 5Gbps signaling rate; 3 USB Type-A 480Mbps signaling rate
Power	700 W 92% efficient, wide-ranging, active PFC
Ecolabels	EPEAT® registered
Energy star certified	ENERGY STAR® certified
Management features	HP Driver Packs; HP Management Integration Kit for Microsoft System Center Configuration Management Gen4; HP System Software Manager (download); HP BIOS Configuration Utility (download) ^[18]

Sustainable impact specifications

Ocean-bound plastic in speaker enclosure; 45% post-consumer recycled plastic; 25% ITE-derived closed loop plastic; Bulk packaging available; 80 Plus® Gold power supplies available; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Ocean-bound plastic in speaker enclosure and system fan; Contains recycled metal

Security management

HP Secure Erase; HP Sure Click; HP BIOSphere Gen6; HP Sure Admin; Hood Sensor Optional Kit; HP Client Security Manager Gen6; HP Sure Start Gen7; HP Sure Recover Gen4; HP Sure Sense Gen2; HP Sure Run Gen5^[19,20,21,22,23,24,25,26,33]

Software included

HP PC Hardware Diagnostics UEFI; HP Support Assistant; HP PC Hardware Diagnostics Windows; ZCentral Remote Boost; HP Image Assistant; HP Manageability Integration Kit; Performance Advisor 3.0^[15,16,17]

UPC number

(ABA) 197497708608; (ABC) 197497708615

Additional specifications

ECC memory	non-ECC
Graphic card footnote number	[32]
I/O Port location	Rear
I/O Port location	Front
Keyboard connectivity	wired
Legal tagline	HP recommends Windows 11 Pro for business
Memory and storage	16 GB memory; 512 GB SSD storage
Memory layout (slots & size)	1 x 16 GB
Memory module type	UDIMM
Memory size	16
Memory size uom	GB
Memory speed	4800
Memory speed uom	MHz
Memory type	DDR5
Number of memory slots	1
Playbook TS icon OS	http://h10003.www1.hp.com/digmedialib/prodimg/lowres/c03905482.png
Playbook TS icon battery life	http://h10003.www1.hp.com/digmedialib/prodimg/lowres/c03905264.png
Playbook TS icon connectivity	http://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201987.png
Playbook TS icon dimensions tower	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201997.png
Playbook TS icon graphics	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08169202.png
Playbook TS icon memory	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08267700.png
Playbook TS icon processor	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201972.png
Playbook TS icon storage	http://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08192819.png
Playbook TS icon weight imperial	http://h10003.www1.hp.com/digmedialib/prodimg/lowres/c05790117.png
Playbook TS icon weight metric	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08267650.png
Processor Brand	Intel®
Processor cache	30 MB L3
Processor core	16
Processor family	Core™ i7
Processor frequency technology	Intel® Turbo Boost Technology
Processor generation	13th Generation
Processor maximum frequency	5.2

Processor maximum frequency uom	GHz
Processor model	13700
Processor threads	24
Product long name specifications	HP Z2 Tower G9 Workstation, Windows 11 Pro, Intel® Core™ i7, 16GB RAM, 512GB SSD
Product short name specifications	HP Z2 Tower G9 Workstation, Intel® Core™ i7, 16GB RAM, 512GB SSD
Security Software Licenses	HP Wolf Pro Security Edition (1 year)
Standard memory note	Transfer rates up to 4800 MT/s.
Storage brand 01	HP Z Turbo Drive
Storage capacity	512
Storage capacity uom 01	GB
Storage controller	Integrated SATA (4 ports 6 Gb/s) with integrated RAID 0, 1, for PCIe SSDs supported. Requires identical hard drives (speeds, capacity, interface).
Storage form factor 01	M.2
Storage interface 01	PCIe®
Storage interface protocol 01	NVMe™
Storage memory technology 01	TLC
Storage type	SSD
Storage type 01	SSD
UNSPSC code	43211515

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[15] HP ZCentral Remote Boost does not come preinstalled on Z Workstations but can be downloaded and run on all Z desktop and laptops without license purchase. With non-Z sender devices, purchase of perpetual individual license or perpetual floating license per simultaneously executing versions and purchase of ZCentral Remote Boost Software Support is required. ZCentral Remote Boost requires Windows, RHEL (7 or 8), UBUNTU 18.04 LTS, or HP ThinPro 7operating systems. MacOS (10.13 or newer) operating system is only supported on the receiver side. Requires network access. The software is available for download at [hp.com/ZCentralRemoteBoost](http.com/ZCentralRemoteBoost).

[16] HP Performance Advisor Software - HP Performance Advisor is ready and waiting to help you get the most out of your HP Workstation from day one—and every day after. Learn more or download at: <https://www8.hp.com/us/en/workstations/performance-advisor.html>

[17] HP Support Assistant requires Windows and Internet access.

[18] HP Manageability Integration Kit can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/overview.html>

[19] HP Client Security Manager Gen7 requires Windows and is available on the select HP PCs.

[20] HP BIOSphere Gen6 features may vary depending on the platform and configurations.

[21] HP Sure Click requires Windows 11 Pro or Enterprise. See https://bit.ly/2PrLT6A_SureClick for complete details.

[22] HP Sure Start Gen7 is available on select HP PCs and workstations. See product specifications for availability.

[23] HP Sure Run Gen5 is available on select HP PCs and requires Windows 10 and higher.

[24] HP Sure Recover Gen4 is available on select HP PCs and requires an open network connection. You must back up important files, data, photos, videos, etc. before using HP Sure Recover to avoid loss of data.

[25] HP Secure Erase for the methods outlined in the National Institute of Standards and Technology Special Publication 800-88 "Clear" sanitation method. HP Secure Erase does not support platforms with Intel® Optane™.

[26] HP Sure Sense requires Windows 11 Pro or Enterprise and supports Microsoft Internet Explorer, Google Chrome™, and Chromium™. Supported attachments include Microsoft Office (Word, Excel, PowerPoint) and PDF files in read only mode, when Microsoft Office or Adobe Acrobat are installed.

[33] HP Sure Admin requires Windows 10 or higher, HP BIOS, HP Manageability Integration Kit from <http://www.hp.com/go/clientmanagement> and HP Sure Admin Local Access Authenticator smartphone app from the Android or Apple store.

Disclaimer — Copyright

Intel, Pentium, the Intel logo, Intel Core, Thunderbolt, vPro, Optane, and Core Inside are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark of its proprietor, used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. Adobe PDF is a trademark of Adobe Systems Incorporated. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. NVIDIA, the NVIDIA logo, Quadro, and GeForce are trademarks and/or registered trademarks of NVIDIA Corporation in the US. and other countries. Bluetooth is a trademark of its proprietor and used by HP Inc. under license. AMD and Radeon are trademarks of Advanced Micro Devices, Inc. All other trademarks are the property of their respective owners.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.