

PERFORMANCE

Processor

Intel® Core™ i5-13500H, 12C (4P + 8E) / 16T, P-core 2.6 / 4.7GHz, E-core 1.9 / 3.5GHz, 18MB

Graphics

NVIDIA® GeForce RTX™ 4050 6GB GDDR6

Chipset

Intel SoC Platform

Memory

2x 8GB SO-DIMM DDR5-5200

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Max Memory

Up to 32GB DDR5-5200 offering

Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe®

Storage Support⁽¹⁾

Up to two drives, 2x M.2 SSD

- M.2 2280 SSD up to 1TB

Storage Slot

Two M.2 slots

- One M.2 2242 PCIe 4.0 x4 slot
- One M.2 2280 PCIe 4.0 x4 slot

Card Reader

SD Express 7.0 Card Reader

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC3306-CG codec

Speakers

Stereo speakers, 2W x2 woofers and 2W x2 tweeters, Dolby® Atmos®, sound by harman/kardon, Smart Amplifier (AMP)

Camera

FHD 1080p + IR Hybrid with Privacy Shutter

Microphone

2x, Array

Battery

Integrated 80Wh

Max Battery Life

MobileMark® 2018: 10.5 hr

Local video (1080p) playback@150nits: 18 hr

Power Adapter

230W Slim Tip (3-pin)

Special Features

AI Chip: LA2-Q

DESIGN

Display

16" WQXGA (2560x1600) IPS 400nits Anti-glare, 100% sRGB, 60Hz, Dolby Vision™

Touchscreen

None

Color Calibration

Factory Color Calibration

Keyboard

Backlit, English (US)

Case Color

Storm Grey

Surface Treatment

Anodizing Sandblasting

Case Material

Aluminium (Top), Aluminium (Bottom)

Dimensions (WxDxH)

354.6 x 255 x 19.9 mm (13.96 x 10.04 x 0.78 inches)

Weight

Around 2.2 kg (4.85 lbs)

SOFTWARE

Operating System

Windows® 11 Pro, English

Bundled Software

Office Trial

CONNECTIVITY

Ethernet

No Onboard Ethernet

WLAN + Bluetooth®

Wi-Fi® 6, 11ax 2x2 + BT5.1

Standard Ports

- 2x USB 3.2 Gen 2
- 1x USB-C® 3.2 Gen 2 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)
- 1x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort 1.4)
- 1x HDMI®, up to 8K/60Hz
- 1x SD card reader
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

Optional Ports (configured)

None

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0 Enabled

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security

- Camera privacy shutter
- IR camera for Windows® Hello

MANAGEABILITY

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

None

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- FSC certified package
- EPEAT™ Gold Registered
- ENERGY STAR® 8.0
- ErP Lot 6
- ErP Lot 26
- TCO Certified 9.0
- RoHS compliant
- Low-VOC

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Low Blue Light (Hardware Solution)

Mil-Spec Test

MIL-STD-810H military test passed

MODEL

TopSeller : Yes **Announce Date** : 2023-05-04

EAN / UPC / JAN : 197528257365 **End of Support** : 2029-11-14

To see more note information, please link to

https://psref.lenovo.com/Detail/ThinkBook_16p_G4_IRH?M=21J8002LUS.

· Lenovo reserves the right to change specifications or other product information without notice.

· Battery life is an estimated maximum. Actual battery life may vary by hardware or system settings, active applications, battery conditioning, etc.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39180)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WS0T36151)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A23681)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference