

4-Port VGA KVM Switch with Built-In VGA, USB and 3.5 mm Audio Cables

MODEL NUMBER: B032-VUA4



Lets you access and control up to 4 computers using one VGA monitor and one USB keyboard and mouse.

Features

Connects 4 Computers to a VGA Monitor and a Single Keyboard/Mouse

This single-monitor KVM switch lets you connect as many as four computers, which you can access and control by toggling between them. All connected computers share one VGA monitor and one USB keyboard/mouse, which saves space on your desk or workspace. Built-in four-foot (1.2-meter) VGA, USB and audio cables save you the expense and effort of buying separate cable kits for each computer. The B032-VUA4 supports video resolutions up to 2048 x 1536 (DDC2B) on a VGA monitor (P502-006-SM VGA coaxial cable sold separately).

Switching Between Computers Is Fast and Easy

Use hotkey commands or a connected mouse for quick and easy switching among computers. You can also use the Auto Scan feature to scan all connected computers automatically in five-second intervals. Port LEDs indicate which computer is currently selected. Computers may be added, removed or replaced without disconnecting or rebooting other connected computers.

Optional USB Hub Lets You Share Peripherals between Computers

Connecting an optional USB hub (sold separately) to the USB console mouse port lets you share USB peripherals, such as printers, hard drives, scanners and webcams, between all connected computers. This lets you avoid the expense and clutter of separate USB hubs.

Simple Plug-and-Play Installation and Operation

The heavy-duty metal housing can be placed on a desktop or other level surface that safely supports the weight of the KVM switch and attached cables. It requires no extra software, external power or other complicated setup procedures. It works with any computer with available VGA and USB ports (the UR024-001 USB cable is an optional accessory). It also works with gaming keyboards and wireless keyboards/mice.

Specifications

OVERVIEW

Highlights

- Features built-in 4 ft. VGA, USB and audio cables for connecting to computers
- Hotkeys allow fast, easy toggling between connected computers
- Connect a VGA monitor with P502-006-SM cable for 2048 x 1536 (DDC2B) resolutions
- Connect USB peripherals for sharing via optional USB hub or USB cable
- Works with all major operating systems, including Windows, macOS and Linux

System Requirements

- VGA, SVGA or Multisync monitor (P502-006-SM cable recommended)
- USB keyboard/mouse
- Computer(s) with VGA output and USB-A ports

Package Includes

- B032-VUA4 4-Port VGA KVM Switch
- Quick Start Guide

| | |
|--|--|
| UPC Code | 037332279798 |
| Product Type | USB VGA/AUDIO CABLE KVM SWITCH |
| Max CPU | 4 |
| Technology | Stereo Audio; USB; VGA/SVGA |
| VIDEO | |
| Max Supported Video Resolution | 2048 x 1536; DDC2B |
| INPUT | |
| Voltage Compatibility (VDC) | 5 |
| Redundancy - Dual Power Inputs | No |
| Bus Powered | No |
| POWER | |
| Power Consumption (Watts) | 0.90 |
| USER INTERFACE, ALERTS & CONTROLS | |
| LED Indicators | Port 1 Online (Green) indicate that the computer attached to its corresponding port is the one that has the KVM focus Port 2 Online (Green) indicate that the computer attached to its corresponding port is the one that has the KVM focus Port 3 Online (Green) indicate that the computer attached to its corresponding port is the one that has the KVM focus Port 4 Online (Green) indicate that the computer attached to its corresponding port is the one that has the KVM focus |
| PHYSICAL | |
| Color | Black |
| Material of Construction | Plastic |
| Rackmountable | No |
| Shipping Dimensions (hwd / in.) | 11.14 x 2.44 x 6.81 |
| Shipping Dimensions (hwd / cm) | 28.30 x 6.20 x 17.30 |
| Shipping Weight (lbs.) | 1.68 |
| Shipping Weight (kg) | 0.76 |
| Unit Dimensions (hwd / in.) | 9.685 x 38.420 x 37.000 |
| Unit Dimensions (hwd / cm) | 24.60 x 97.59 x 93.99 |
| Unit Packaging Type | Box |
| Unit Weight (lbs.) | 1.28 |
| Unit Weight (kg) | 0.58 |
| ENVIRONMENTAL | |

| | |
|---------------------------------------|---|
| Operating Temperature Range | 32° to 122°F (0° to 50°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Relative Humidity | 0 to 80% RH, Non-condensing |
| BTUs | 8 |
| COMMUNICATIONS | |
| Port Control | Hotkey, Mouse Port |
| IP Remote Access | No |
| CONNECTIONS | |
| Number of Ports | 4 |
| PC/Server Connections | PS/2; USB; VGA |
| Side A - Connector 1 | (1) 3.5MM (MALE); (1) HD15 (FEMALE); (2) USB A (FEMALE) |
| Side B - Connector 1 | (4) 3.5MM (MALE); (4) HD15 (MALE); (4) USB A (FEMALE) |
| Computer Keyboard and Mouse Interface | USB |
| Computer Monitor Interface | VGA |
| Console Keyboard and Mouse Interface | USB |
| Console Monitor Interface | VGA |
| FEATURES & SPECIFICATIONS | |
| NIAP-Certified Secure | No |
| Number of Users | 1 |
| On-Screen Display (OSD) | No |
| Driver Required | No |
| REMOTE ACCESS | |
| Modem Port | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | CE (Europe); FCC (USA); RoHS; UKCA; WEEE |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.