



L A P T O P S

## Thin GF63

THIN GF63 12UCX-484US

## Specification

<b>Manufacturer Part #</b>	THINGF6312484
<b>OS</b>	Windows 11 Home (MSI recommends Windows 11 Pro for business)
<b>CPU</b>	Intel® Core™ i5-12450H 4+4Core
<b>CPU Speed</b>	1.3-4.4GHz
<b>Chipset</b>	-
<b>Color</b>	Black
<b>Screen Size</b>	15.6" FHD, IPS-Level 144Hz 45% NTSC
<b>Resolution</b>	1920x1080 16:9
<b>GPU</b>	NVIDIA® GeForce RTX™ 2050 Laptop GPU
<b>Video Memory</b>	4G GDDR6
<b>Keyboard</b>	Red keyboard with Anti-Ghost key (99 Key)
<b>Speaker</b>	2x Speakers 2W
<b>Memory</b>	8GB (8G*1) DDR4 3200MHz
<b>HDD Capacity</b>	512GB NVMe SSD
<b>HDD Interface</b>	NVMe
<b>LAN</b>	Gb LAN
<b>WLAN</b>	Intel Wi-Fi 6 AX201(2*2 ax)
<b>Bluetooth</b>	BT 5.2
<b>Card Reader</b>	-
<b>Webcam</b>	720p HD Webcam
<b>USB</b>	2x USB 3.2 Gen1
<b>Type-C Port</b>	1x USB 3.2 Gen1 w/DP1.4
<b>Video Port</b>	HDMI 4K @ 30Hz
<b>Audio Port</b>	1 Mic in/ 1 headphone out
<b>AC Power Adaptor</b>	120W
<b>Battery Pack</b>	3 cell , 51Whr Li-Polymer
<b>Dimension</b>	14.13"x9.99"x0.85"
<b>Weight</b>	4.10 lbs
<b>Manufacturer Warranty</b>	1 year Limited warranty (Include 1 Year Global)