

## Key Features

- True 4K HDR immersive visual experience
- Advanced LED technology with 30,000 hours lifespan
- 2,900 Lumens for bright and clear images in any environment
- Easy Setup: 0.69-0.83 short throw ratio with H/V keystone & 4 corner adjustment
- Designed for Xbox for ultimate gaming experience



## Product **Description**

Combining true 4K UHD resolution with HDR/HLG support, theater-level sound by Harman Kardon speaker and flexible installation capabilities, the X2-4K is a bright choice for home entertainment. Powered by the advanced 3rd generation LED technology, it offers a 30,000-hour lifespan without the hassle of frequent lamp replacement and toxic mercury, while delivering an impressive visual quality with high brightness of 2,900 Lumens and vibrant colors covering 125% Rec.709. The Harman Kardon dual speaker sets offer upgraded audiovisual enjoyment anytime anywhere. With a 0.69-0.83 short throw ratio, you can go big even in small spaces and experience a 100" display from only 1.5m away. Featuring auto V, H/V keystone, and 4 corner adjustment capabilities, setting up is a breeze, even with limited angles. Screen mirroring via Wi-Fi also makes content streaming easier than ever and the Bluetooth connectivity enables additional audio options, offering an even more intuitive and convenient user experience. The X2-4K is also the world's first projector that is Designed for Xbox, providing the ultimate gaming experience.

Visit Us www.viewsonic.com

**SPECIFICATION OTHERS** 

Native Resolution: 3840x2160 100-240V+/- 10%, 50/60Hz Power Supply Voltage:

Brightness: 2900 (Lumens) (AC in)

Contrast Ratio: 3000000:1 Normal: 236W Power Consumption:

Standby: <0.5W Display Color: 1.07 Billion Colors

0~40°C Operating Temperature: Light Source Type: LED Carton: Color Light Source Life (hours) with 60000 Normal Mode:

Net Weight: 3.6kg F=2.53-2.73, Gross Weight: 5.5kg Lens:

f=10.20-12.25mm Dimensions (WxDxH) with 355x251x121mm 105%+/-5% Projection Offset: Adjustment Foot:

Throw Ratio: 0.69-0.83

Packing Dimensions: 490x376x313mm

Optical Zoom: 1.2X English, French, Spanish, Thai, Digital Zoom: 0.8x-2.0x Korean, German, Italian, Russian, Image Size: 60"-120" Swedish, Dutch,

Polish, Czech, 0.92m-2.2m Throw Distance: T-Chinese, (100"@1.53m) OSD Language:

S-Chinese, Japanese, Turkish, Keystone: H:+/-40°, V:+/-40°

Portuguese, Finnish, Audible Noise (Normal): 33dB Indonesian, India, Arabic, Vietnamese, Audible Noise (Eco): 29dB Greek, Hungarian

Total 24 languages Total 16GB Local Storage: (12GB available English, S-Chinese,

storage) T-Chinese, Indonesian, Finish, Input Lag: 4.2ms French, German,

Italian, Japanese, VGA(640 x 480) to Resolution Support: Korean, Polish, 4K(3840 x 2160) User Guide Language: Portuguese, Russian,

Spanish, Swedish, 480i, 480p, 576i, Turkish, Arabic, **HDTV** Compatibility: 576p, 720p, 1080i, Czech, Thai, 1080p, 2160p Vietnamese, total 20

1

Horizontal Frequency: 15K-135KHz languages

STANDARD ACCESSORY Vertical Scan Rate: 23-240Hz

Power Cord: **INPUT** USB-C Cable:

1 (1m) HDMI: (HDMI 2.0, HDCP 1.4/2.2)Remote Control:

(BT w/ backlit)

USB Type C: 1 (5V/1A) QSG: Yes

1 (BT4.2) Audio-in (Bluetooth): Warranty Card: Yes (CN Only)

USB Type A: **OPTIONAL ACCESSORY** 

(USB2.0 Reader) Wall/Ceiling Mount: PJ-WMK-007

Wifi Input: 1 (5Gn) Carry Bag: PJ-CASE-009

**OUTPUT** 

Audio-out (3.5mm): 1

6W Cube x2 Speaker: (Full range x2)

(USB2.0 - 5V/1A x1, USB Type A (Power): share with USB A

Input)

Audio-out (Bluetooth):

**CONTROL** 

RS232 (DB 9-pin male): 1 USB Type A (Services): 1

1 (BT4.2)