



# **10GBASE-T to SFP+ Fiber Media Converter**

TFC-10GSFP (v1.0R)

- 1 x 10G RJ-45 port
- 1 x 10G SFP+ Slot
- LFPT support (Link Fault Pass Through)
- · SFP slot accommodates multimode or single-mode modules
- Auto-MDIX RJ-45 port supports full-duplex mode
- Functions as a standalone converter
- NDAA / TAA compliant (U.S. and Canada only)

TRENDnet's compact 10GBASE-T to SFP Fiber Media Converter, model TEG-10GSFP, converts a 10GBASE-T (Copper 10Gbps) ethernet connection to 10G BASE-SX/LX (Fiber) SFP media connection , and vice versa. The 10GBASE-T RJ-45 port on the 10G SFP+ transceiver supports a full-duplex 10G connection at wire speed. The SFP slot supports both multimode (SX) or single-mode (LX) SFP modules.





Multi-Gig Slot The SFP and RJ-45 ports support 10G, 5G, 2.5G, and 1G speeds.



**Power Adapter** A power adapter is included with the 10G SFP+ transceiver for standalone use.



**Compact** Compact and lightweight metal housing design provides greater installation flexibility.

# **FEATURES**

ſ					
	П	П	I	I	1
11	ኣ			s	1
U					

## Multi-Gig Ethernet

1 x 10G/5G/2.5G/1G Ethernet port



Multi-Gig SFP 1 x 10G/5G/2.5G/1G SFP+ slot



## Fanless

Fanless design on the 10G SFP+ media converter lowers energy consumption and eliminates operating noise

$\mathbf{N}$	$\checkmark$
<i></i>	./

## Compact Design

Small, compact, and lightweight metal housing of the 10GbE SFP+ transceiver provides greater installation flexibility



## LED Indicators

LED indicators convey port status





## Fiber Wavelength

The 10G SFP+ transceiver is compatible with multi-mode and single mode transmissions



# **NETWORKING SOLUTION**





# TRENDNET

## **SPECIFICATIONS**

#### Standards

- IEEE 802.3
- IEEE 802.3u
- IEEE 802.3ab
- IEEE 802.3an
- IEEE 802.3bz
- IEEE 802.3z

#### **Device Interface**

- 1 x 10G/5G/2.5G/1G ethernet port
- 1 x 10G/5G/2.5G/1G SFP+ slot
- LED indicators

#### Data Transfer Rate

- Gigabit: 2000Mbps (full duplex)
- 2.5G: 5000Mbps (full duplex)
- 5G: 10Gbps (full duplex)
- 10G: 20Gbps (full duplex)

#### **Special Features**

- Supports Link Fault Pass-Through (LFPT)
- SFP slot supports Multimode and Single mode Modules

#### Power

- Input: 110 240 V AC, 50/60 Hz 0.5A
- Output: 5V DC, 1.5A
- Max. consumption: 4W

#### **Operating Temperature**

• 0° C – 50° C (32° F – 122° F)

#### **Operating Humidity**

• Max. 90% non-condensing

#### Dimensions

• 105 x 75 x 22 mm (4.13 x 2.95 x 0.86 in.)

#### Weight

• 188 g (6.63 oz.)

#### Certifications

- CE
- FCC

#### Warranty

• 3 year

#### **Package Contents**

- TFC-10GSFP
- Quick Installation Guide
- Power Adapter (5V DC, 1.5A)

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.

20675 Manhattan Place • Torrance • CA 90501 • USA • T: 1-888-326-6061 • sales@trendnet.com • www.TRENDnet.com

TRENDnet is a registered trademark. Other Brands and product names are trademarks of their respective holders. Information provided in this document pertain to TRENDnet products and is subject to change at any time, without notice. For the most recent product information please visit http://www.trendnet.com. Copyright © TRENDnet. All Rights Reserved.

TFC-10GSFP