



Poly Savi 8210 UC Microsoft Teams Certified DECT 1920-1930 MHz USB-A Headset (77T31AA)



Overview

Perfect calls, now portable.

Hybrid workers, get ready for true wireless freedom. The portable, comfortable Poly Savi 8200 UC Series headset with close conversation limiting noise cancellation offers long-range DECT™ technology with USB plug-and-play convenience.

Wireless freedom

Stay productive while still enjoying the freedom to move around. Long-range interference-free wireless DECT™ technology makes sure your calls are clear, even up to 137 m / 450 ft.[1] away from your desk.

Keep conversations clear

These light headsets tune out nearby noise and keep every conversation secure, private, and clear with close conversation limiting noise cancellation. Whether in the office or at home, the Savi 8200 UC Series keeps you sounding your best all day.

Features

DECT™ security-certified headset

Privacy of your conversation is ensured: DECT™ Security-certified headset.

Noise-canceling microphone with close conversation limiting

Block background sounds with noise-canceling microphone and close conversation limiting.

Flexible microphone boom and positioning guides

Optimize your audio quality with flexible microphone boom and positioning guides.

SoundGuard DIGITAL Sound leveling and acoustic limiting

Optimal listening comfort with SoundGuard Digital sound leveling and acoustic limiting that protects against sounds above 118 dBA.

[1] Line of sight from computer.

Additional specifications

| | |
|---|---|
| Acoustic protection technology | SoundGuard Digital ^[1,2] |
| Audio | Noise and echo reduction |
| Battery life | >13 hours (talk time, over-the-head); >50 hours (standby time) |
| Battery type | Rechargeable Li-ion polymer |
| Bluetooth version | 4.2 |
| Button user controls | Power on/off; Call answer/end; Mute; Volume +/- |
| Cartons per layer | 10 |
| Cartons per pallet | 80 |
| Certified collaboration software | Zoom |
| Charge time | 3 hours |
| Color | Black |
| Connection type | USB Type-A/C® |
| Connection type | DECT™ |
| Connectivity | DECT™ USB adapter |
| Connects to | PC |
| Country of origin | Made in Mexico |
| Datasheet photo 1 | https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c08399843.png |
| Datasheet photo 2 | https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c08399813.png |
| Datasheet photo 3 | https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c08399753.png |
| ECCN | 5A992 |
| Ear cushions | PC (polycarbonate) (surface material) |
| HTS code | 8517620090 |
| Headphone type | On-ear (monoaural) |
| Impedance | 32 ohms |
| Indicator light | On call |
| Management Software | Plantronics Hub (desktop) |
| Manufacturer Warranty | Poly standard two-year limited warranty |
| Microphone bandwidth | 35 Hz to 21 kHz |
| Microphone type | Omnidirectional |
| Minimum dimensions (W x D x H) | 15.5 x 16.6 x 6.7 cm |
| Minimum dimensions (W x D x H) | 6.1 x 6.53 x 2.63 in |

| | |
|---------------------------------------|--|
| Minimum order quantity | 5 |
| Package dimensions (W x D x H) | 21 x 18.5 x 11.5 cm |
| Package dimensions (W x D x H) | 7.28 x 8.26 x 4.52 in |
| Package weight | 646.42 g |
| Package weight | 1.42 lb |
| Paired devices | Up to 2 |
| Pallet (layers) | 8 |
| Pallet dimensions | 48 x 40 x 76.7 in |
| Pallet dimensions (W x D x H) | 121.9 x 101.6 x 194.8 cm |
| Pallet weight | 313.4 kg |
| Pallet weight | 690.92 lb |
| Products per pallet | 400 |
| Products per pallet layer | 50 |
| Sensitivity (microphone) | -40 +/-3 dB |
| Signal-to-noise ratio | >53 dB |
| Speaker size | 32 mm |
| Special features | Adjustable headband |
| Supported bluetooth profiles | AVRCP 1.6 |
| UC compatibility | Microsoft |
| UNSPSC code | 43191609 |
| UPC number | (ABA) 197029593146; (AC3) 197029593153 |
| Voice alerts | Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low |
| Wearing style | Mono |
| Weight | 115 g |
| Weight | 0.25 lb |
| What's in the box | Charging stand; Wireless headset; USB charging cable; Travel case; USB Type-A DECT™ adapter; USB Type-A to USB Type-C® adapter |
| Wireless range | Up to 180 m in open area; Up to 55 m in typical office environment |
| Wireless range (imperial) | Up to 590 ft in open area; Up to 180 ft in typical office environment |

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.



Services

Poly Services

★ : Recommended

Poly Support Services

| | |
|-----------------------------------|-------------------|
| 3 year Poly+ Savi Service | PSAVI312 ★ |
| 3 year Partner Poly+ Savi Service | PSAVI362 |

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

| | |
|--|---------|
| Poly APA-23 Electronic Hookswitch TAA | 85Q50AA |
| Poly APA-24 Electronic Hookswitch TAA | 85Q52AA |
| Poly APC-43 Electronic Hookswitch (Bagged) TAA | 85Q56AA |
| Poly APC-43 Electronic Hookswitch TAA | 85Q55AA |
| Poly APC-45 Electronic Hookswitch TAA | 85Q57AA |
| Poly APC-82 Electronic Hookswitch TAA | 8H981AA |
| Poly APD-80 Electronic Hookswitch TAA | 85Q58AA |
| Poly APN-91 Electronic Hookswitch TAA | 85Q59AA |
| Poly APP-51 Electronic Hookswitch TAA | 85Q60AA |
| Poly APS-11 Electronic Hookswitch TAA | 85Q78AA |
| Poly APT-31 Electronic Hookswitch TAA | 85Q84AA |
| Poly APU-72 Electronic Hookswitch TAA | 85Q95AA |
| Poly APU-75D Electronic Hookswitch TAA | 85Q99AA |
| Poly APU-76 Electronic Hookswitch TAA | 85R00AA |
| Poly APV-63 Electronic Hookswitch TAA | 85R01AA |
| Poly APV-66 Electronic Hookswitch TAA | 85R02AA |
| Poly EHS 3.5mm to 3.5mm Cable | 85R17AA |
| Poly HL10 Extended Arm | 8L554AA |
| Poly HL10 Handset Lifter | 784Q1AA |
| Poly HL10 Handset Lifter TAA | 8R713AA |
| Poly HL10 Handset Lifter with Straight Plug TAA | 784Q2AA |
| Poly HL10 Lifter Arm +Ring Detector Accessory | 8A7E3AA |
| Poly RD-1 Electronic Hookswitch | 85R71AA |
| Poly Savi 7410/7420 Office Charging Cradle | 8L556AA |
| Poly Savi 8200 5 Unit Charge Base | 85R34AA |
| Poly Savi 8200 Leatherette Ear Cushions (2 Pieces) | 85Q63AA |
| Poly Savi 8200 USB-A Headset Charging Cable | 85R35AA |
| Poly Savi 8210 Battery with Removal Tool | 85R37AA |
| Poly Savi 8210/8220 Universal Power Supply -9V 500mA | 783M9AA |
| Poly Savi 8220 Battery with Removal Tool | 85R39AA |

| | |
|--|---------|
| Poly Savi 8240/8245 Battery | 85R41AA |
| Poly Savi 8240/8245 Deluxe Charging Cradle | 85R44AA |
| Poly Savi 8240/8245 Fit | 85R45AA |
| Poly Savi 8240/8245 Foam Sleeves for Earloop (20 Pieces) | 85Q65AA |
| Poly Savi 8240/8245 Standard Charging Cradle | 85R47AA |
| Poly Savi 8240/8245 USB-A Charging Cable for Headset and Battery | 85R43AA |
| Poly Savi 8245 Deluxe Cradle with Battery | 85R49AA |
| Poly Savi 8245 Headset Cradle and Wearing Accessories | 85T32AA |
| Poly Savi 8400/7400 Office DECT 1920-1930 MHz Base | 8L571AA |
| Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1920-1930 MHz Base | 8L562AA |
| Poly Savi 8410/8420 Office Charging Cradle | 8L573AA |
| Poly Savi 8440/8445 Office Charging Cradle | 8L577AA |
| Poly Savi D400 UC DECT 1920-1930 MHz Dongle | 85T33AA |
| Poly Savi D400 UC Microsoft Teams Certified DECT 1920-1930 MHz Dongle | 85T34AA |
| Poly Savi Hard Case | 85R51AA |
| Poly Savi Office Power Supply with Right Angled Plug -9V 1000mA | 8L5A2AA |
| Poly Savi Office S2 Telephone Cable | 85R55AA |
| Poly Savi Office Straight Plug Online Indicator | 85R52AA |
| Poly Savi Office Telephone Interface Cable | 85R57AA |
| Poly Savi Office USB-A PC Connection Cable | 85R54AA |
| Poly Savi Office Universal AC Power Supply with Straight Plug -9V 1000mA | 85R59AA |
| Poly Savi Office Universal AC Power Supply with Straight Plug -9V 500mA | 85R61AA |
| Poly Savi W8210/8220 Charging Cradle | 85R65AA |
| Poly TR-11 Electronic Hookswitch | 85R84AA |
| Poly USB-A to USB-C Adapter | 85Q48AA |
| Poly USB-C to USB-A Adapter | 85Q49AA |

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.