



Poly Blackwire C3220 Stereo USB-C Headset +Carry Case (80S07AA)

Overview

Freedom to work your way

The Blackwire 3200 Series provides a quality audio experience in a headset that's built for enterprise needs. With a sleek design and flexible microphone boom for a customizable fit, what's not to love?

Poly signature audio quality

Experience the high-quality audio you expect from Poly with a headset that offers PC wideband, a noise-canceling mic, and hi-fi stereo sound options. Dynamic EQ optimizes call quality and automatically adjusts the settings for listening to multimedia.

Long-lasting comfort and portability

Relax while you talk knowing your headset is secure- lightweight metal headband offers durability plus a custom fit. Leatherette ear cushions fold flat for easy portability.

Advanced connectivity

Ideal for managing calls on your PC, mobile phone, or tablet combined with the comfort and durability of a corded headset for greater flexibility.

Additional specifications

Acoustic protection technology	SoundGuard ^[1]
Audio	Dynamic EQ optimized; Digital signal processing (DSP); Noise cancellation (NC)
Boom mic length (ft)	0.43 ft
Boom mic length (mm)	130 mm
Boom mic rotation	270°
Button user controls	Call answer/ignore/end/hold; Redial; Mute; Volume +/-
Cable length	79 cm (inline module to headset); 90 cm (USB to inline module); 161 cm (total USB to headset)
Cable length (imperial)	2.59 ft (inline module to headset); 2.95 ft (USB to inline module); 5.28 ft (total USB to headset)
Certified collaboration software	Skype for Business; Cisco Jabber; Avaya
Color	Black
Compatibility	Compatible with PCs via USB/USB Type-C®, connects to mobile devices and tablets via 3.5 mm and devices that support USB Type-C®
Compatible Operating Systems	Windows 11; Windows 10; macOS
Connection type	Wired USB Type-C®
Ear cushions	Artificial leather (surface material)
Headphone type	On-ear (stereo)
Impedance	32 ohms
Management Software	HP Headset Control Center
Manufacturer Warranty	Poly standard two-year limited warranty
Microphone bandwidth	100 Hz to 10 kHz
Microphone type	Omnidirectional
Minimum System Requirements	USB Type-C® port
Minimum dimensions (W x D x H)	6.1 x 1.25 x 7.1 in
Minimum dimensions (W x D x H)	155 x 32 x 178 mm
Package dimensions (W x D x H)	185 x 56 x 207 mm
Package dimensions (W x D x H)	7.28 x 2.2 x 8.14 in
Package weight	250 g
Package weight	0.55 lb
Sensitivity (microphone)	-38 dBV/Pa
Sensitivity (speaker)	90 dB
Signal-to-noise ratio	>118 dB
Speaker size	28 mm

Special features	Adjustable headband; Voice alerts
UNSPSC code	43191638
Weight	0.19 lb (with cable); 0.14 lb (without cable)
Weight	87 g (with cable); 64 g (without cable)
What's in the box	USB Type-C® cable; Headset; Travel case

[1] Protects against Acoustic Shock by limiting sounds to below 118 dBA.

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Sep 26, 2023 4:54 PM UTC+0000