

Overview

Reliable coverage, all around

Keep the conversation going whenever, wherever in the office with the Poly Rove 30 wireless DECT ™ IP phone solution. It stays cleaner for longer with Microban® antimicrobial product protection and has the flexibility to scale as you grow [1,2].

Ruggedized protection

Keep your onsite employees productive with handsets that include ruggedized and Microban® antimicrobial protection built to withstand all that life throws at it. Drops, dust, water — these pro-grade handsets will go the distance [1,2,3].

You grow, we scale

You don't have to worry about outgrowing your communication solution or feel held back by its options. Poly Rove 30 wireless DECT™ IP phone solution has flexibility to scale with handsets, bases, and repeaters as your organization grows.

Features

Durable IP65-rated handsets

Maintain confidence that your devices will last and that your investment is protected: The ruggedized handsets are drop proof and IP65 dust-tight and water resistant.^[3]

Microban® protection

Rest assured that your devices, enhanced with Microban® antimicrobial product protection, stay cleaner, fresher and more durable for longer. Protection that lasts the life of the product, actively reducing the growth of bacteria. [1,2]

Privacy is ensured

Conversations are safe and secure with DECT™ wireless security. And it doesn't stop there - maintain DECT™ encryption even when you add a base or repeater to your solution.

Long-lasting battery power

Enable employees on the move to communicate more effectively, respond faster to requests and alerts, and be more productive with up to 18 hours of talk time and up to 300 hours of standby time.

Grab a Poly headset and go

Communicate hands-free with a Poly wired headset using the dedicated 3.5 mm connection. Perfect for users who feel more comfortable wearing a headset.

Easy-to-clean handsets

Ideal for healthcare environments, these handsets are specifically designed for easy cleaning with smooth surfaces and no gaps between buttons.

[1] Microban antimicrobial product protection is a built-in active ingredient that enables products to resist the growth of microbes such as bacteria, mold, and mildew. Microban protection helps products stay cleaner, fresher, and last longer than products with untreated surfaces.

[2] Microban antimicrobial product protection available for the Poly Rove 30 handset models.

[3] Poly Rove 30 ruggedized handsets are drop proof (up to 6.6 ft/2 m) and IP65 dust-tight and water resistant.

Additional specifications

Audio	DTMF tone generation (RFC 2833 and in-band)	
Audio codecs	G.165, 168 echo cancellation	
Battery life	Up to 18 hours (talk time); Up to 300 hours (standby time)	
Battery type	Rechargeable Li-ion	
Certifications and compliances	UL 62368-1	
Certified collaboration software	Zoom	
Color	Black	
Country of origin	Product of China	
DECT frequency	1920 to 1930 MHz	
Display features	Adjustable font size selection (regular, medium, large)	
Display size (diagonal)	6.1 cm (2.4")	
Display size (diagonal)	2.4"	
Energy star certified	ENERGY STAR® certified	
Headset and handset compatibility	Compliant with ADA Section 508 Subpart B 1194.23 (all)	
Headset ports	1 3.5 mm headset jack	
Management Software	Polycom Device Management Service for Service Providers (PDMS-SP) Cloud Management	
Manufacturer Warranty	Poly standard one-year limited warranty	
Minimum dimensions (W \times D \times H)	56.9 x 146.3 x 36.8 mm	
Minimum dimensions (W \times D \times H)	2.2 x 5.8 x 1.5 in	
Native resolution	240 x 320	
Onscreen controls	Three multi-colored mute indicators; Three sets of capacitive touch volume and mute buttons	
Operating humidity range	5 to 95%	
Operating temperature range	-10 to 55℃	
Operating temperature range	14 to 131°F	
Package dimensions (W x D x H)	176 x 163 x 44 mm	
Package dimensions (W x D x H)	6.9 x 6.4 x 1.7 in	
Package weight	365 g	
Package weight	0.8 lb	
Panel technology	Color TFT LCD	
Power	External universal AC adapter: 5V 1A DC	
Security management	DECT™ security certified	

Special features	Unicode UTF-8 character support; Push-to-talk
Storage temperature range	-40 to 158°F
Storage temperature range	-40 to 70℃
Telephony and call handling features	4 line keys
UNSPSC code	43191606
UPC number	(ABA) 197497527476; (ABB) 197497527483; (ABG) 197497527490; (ABJ) 197497775334; (ABU) 197497527513; (UUF) 196548115594
VoIP features	Up to Twenty (20) service subscription profile assignments (SP 1 $-$ 20)
Weight	0.07.11
Weight	0.37 lb
Weight	0.37 lb 168 g
-	10.0
Weight	168 g Safety information sheet; Handset; Quick start guide; AC power adapter;
Weight What's in the box	168 g Safety information sheet; Handset; Quick start guide; AC power adapter; Charging cradle; Spare battery; Base station; Ethernet cable; Belt clip

Services

Poly Services ★: Recommended

Poly Support Services

3 Year Poly+ Rove 30 Anti Microbial DECT IP Phone Handset	P86930312 ★
1 Year Partner Poly+ Rove 30 Anti Microbial DECT IP Phone Handset	P86930160
1 Year Poly Elite Rove 30 Anti Microbial DECT IP Phone Handset	E86930112
1 Year Poly+ Rove 30 Anti Microbial DECT IP Phone Handset	P86930112
3 Year Partner Poly+ Rove 30 Anti Microbial DECT IP Phone Handset	P86930362
7 Year HWR Rove 40 Anti Microbial DECT IP Phone Handset NBD with Poly DaaS Svc	D7YLLT029

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Dec 11, 2023 4:22 PM UTC+0000