



Poly Voyager Focus 2 Microsoft Teams Certified USB-A Headset (77Y85AA)



Overview

The sweet sound of focus

Create a focus zone around you with the Voyager Focus 2, stereo Bluetooth® headset. Smartly engineered for audio perfection – all you will hear is your call. And the focus stays on you, right where it belongs.

Your focus zone

Experience Poly acoustic excellence with the Voyager Focus 2 headset. Loud and distracting background is reduced with three levels of advanced digital hybrid ANC. You'll be ready to have the most critical conversations with confidence.

Wear it like it's not there

Stay engaged during a full day of calls wearing a comfortable headband with cushioned sling and plush ear cushions. The Voyager Focus 2 is designed with you in mind – stay focused and productive all day.

Crystal clear conversations

It's you – loud and clear. That's all callers hear. The discreet microphone boom is not only ultra-noise canceling but, with its Acoustic Fence technology, literally creates a virtual noise-free bubble in front of your mouth.

Features

Immersive experience

Stay focused while on calls or listening to music/media with stereo sound.

It's your call

Stay productive with up to 19 hours of wireless talk time (ANC on) and extend the battery life by using it corded, with audio over USB mode.

Smart sensors

Dynamic Mute Alert senses and tells you when talking while muted. And the on-ear indicator light flashes to let others around you know you are on a call to keep you distraction free.

Easy to use

An easy-to-use headset with smart sensors for answering/muting calls and playing/pausing music. The intelligent microphone boom automatically maintains left and right audio no matter which side the headset is worn on.

Choose your device

Works with your choice of device: PC via included BT700 USB-A or USB Type-C® Bluetooth® adapter and mobile phones via Bluetooth® v5.1.

Certified for Microsoft Teams

Full Microsoft Teams certification takes your Microsoft Teams experience to the next level with a button for instant access to the app and more.

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Audio	Dynamic EQ optimized
Battery life	Up to 25 hours (talk time, ANC and online indicator off); Up to 20 hours (talk time, ANC and online indicator on); Up to 18 hours (talk time, ANC off and online indicator on, default setting); Up to 16 hours (talk time, ANC on and online indicator on, default setting); Up to 40 hours (music time, ANC off); Up to 24 hours (music time, ANC on); Up to 30 days (standby time) ^[4]
Battery type	Rechargeable Li-ion
Bluetooth version	5.1
Button user controls	Power on/off; Call answer/end; Mute; Volume +/-; Pairing; ANC: off, low, high
Cable length	1.5 m
Cable length (imperial)	59.05 in
Cartons per layer	10
Cartons per pallet	80
Charge time	<2 hours
Charging plug	Micro USB to USB Type-A
Color	Black
Compatibility	Compatible with PCs via included BT700 Bluetooth® adapter or via USB cable; smartphone via Bluetooth®
Compatible Operating Systems	Windows 11; Windows 10; macOS
Connection type	Bluetooth®; USB Type-A; Micro USB (PC)
Connects to	PC; Mobile
Ear cushions	Artificial leather (surface material)
Headphone type	On-ear
Indicator light	Connectivity; On call
Management Software	Poly Lens
Manufacturer Warranty	Poly standard two-year limited warranty
Master carton upc code	10017229171791
Microphone bandwidth	100 Hz to 6.8 kHz
Microphone type	2 analog ECM; 2 digital MEMS
Minimum System Requirements	Bluetooth®; USB Type-A port
Minimum dimensions (W x D x H)	6.1 x 2.6 x 7.2 in
Minimum dimensions (W x D x H)	15.5 x 6.7 x 18.2 cm
Number of microphones	4

Package dimensions (W x D x H)	8.27 x 7.4 x 4.53 in
Package dimensions (W x D x H)	21 x 19 x 11.5 cm
Package weight	0.712 kg
Package weight	1.57 lb
Paired devices	Up to 2
Pallet (layers)	8
Pallet weight	328.43 kg
Pallet weight	724.06 lb
Products per pallet	400
Products per pallet layer	50
Sensitivity (speaker)	N/A
Speaker size	32 mm
Special features	Noise reduction on outgoing voice audio; Multi-connect; Adjustable headband; Adjustable Active Noise Cancellation (ANC); Two LED indicators on speaker in call status
Supported bluetooth profiles	A2DP; AVRCP; HFP; HSP
UNSPSC code	43191638
UPC number	017229171794
Voice alerts	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
Voice assistant	Siri; Google
Weight	0.39 lb
Weight	0.176 kg
What's in the box	Wireless headset; Micro USB charging cable; BT700 Bluetooth® USB adapter; Travel pouch; Quick start guide
Wireless range	Up to 50 m; Up to 91 m (with Voyager Office base) ^[3]
Wireless range (imperial)	Up to 164 ft; Up to 300 ft (with Voyager Office base)

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

[3] Voyager Office Base is available as an accessory and is sold separately.

[4] Online indicator adjustments require a setting change via Poly Lens or Plantronics Hub.

Hybrid Work Solutions

Audio

★ : Recommended

Audio Accessories

Poly BT700 USB-A Bluetooth Adapter	786C4AA
Poly BT700 USB-C Bluetooth Adapter	786C5AA
Poly Micro USB to USB-A Charging Cable	85R53AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA
Poly Voyager Focus 2 Case	786D2AA
Poly Voyager Focus 2 Leatherette Ear Cushions (2 Pieces)	783R8AA
Poly Voyager Microsoft Teams Certified Office Base	786D0AA
Poly Voyager Office Base	786C9AA
Poly Voyager USB-A Charging Stand	783R6AA
Poly Voyager USB-C Charging Stand	783R7AA

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 20, 2023 1:32 PM UTC+0000