



Philips
Bluetooth party speaker

Speaker light and strobe
Mic and guitar inputs
Special karaoke functions



TAX3206

Rock to the beat

Bring the party where you choose with this large, portable speaker. While you rock your guitar, play some tunes, or get on the mic -- colored lights and a strobe pulse on the speaker! A carry handle makes the speaker easy to move.

Get the party started right

- Deep bass. Up to 14 hours play time
- Party light effects. Blaze to the music
- All your tunes. Bluetooth, audio-in, and more
- 2x 2" tweeters. 8" woofer

Rock those skills

- Mic and guitar inputs. Karaoke effects
- USB slot for music playback
- Buttons on speaker for music control, lights, and more
- Rotary knobs for mic, guitar, echo, treble, bass

Take the party with you

- Ready for anything
- AC-powered. Built-in battery for outside play
- Built-in handle
- Dimensions: 30.9x46.05x32.2 cm

PHILIPS

Specifications

Sound

- Output Power: 80W (maximum)
- Output power (RMS): 40W @ 10% THD
- Frequency response: 50Hz - 20KHz, -12dB
- Sound enhancement: treble and bass control, Karaoke

Speaker

- No. of sound channels: Mono
- Tweeter: 2" x 2
- Woofer: 8"

Connectivity

- Mic in: 1 x (6.3mm w/ vol control)
- Guitar input: 1 x (6.3mm w/ vol control)
- USB: Yes (playback, charging and reading, service)
- Line-in: 1 x (3.5mm)
- Line-out: 1 x (3.5mm)
- Bluetooth version: 5.0
- Bluetooth profiles: Streaming Format: SBC, Music streaming (A2DP), Playback/volume control: AVRCP, Multipoint (Multipair) support

Supported Audio Formats

- Bluetooth: SBC
- USB: MP3, WAV, WMA, FLAC

Convenience

- Volume control: Tact switch
- Karaoke: Echo control, MIC volume, vocal fader, voice changer
- Guitar control

Display

- Display Type: LED display screen; Speaker light effect, strobe light

- Backlight: blue
- Charging indicator: red

Power

- Power supply: 100-240VAC, 50/60Hz
- Battery Capacity: 2200 mAh, 7.4 V
- Battery life time: 14 hr
- Charging time: <=3 hr

Accessories

- Included accessories: AC Power Cord, Quick start guide, Warranty certificate, Safety warranty sheet

Product dimensions

- Product dimensions (W x H x D): 30.9 x 46.05 x 32.2 cm
- Product dimensions (W x H x D): 12.2 x 18.1 x 12.7 inch
- Weight: 15.322 lb
- Weight: 6.95 kg

Packaging dimensions

- Packaging dimensions (W x H x D): 15.4 x 20.6 x 14.6 inch
- Packaging dimensions (W x H x D): 39 x 52.2 x 37 cm
- Gross weight: 8.7 kg
- Gross weight: 19.180 lb
- Nett weight: 15.520 lb
- Nett weight: 7.04 kg
- Tare weight: 3.660 lb
- Tare weight: 1.66 kg
- UPC: 8 40063 20188 0
- Number of products included: 1
- Packaging type: Carton
- Type of shelf placement: Standing

Highlights

Deep bass

With powerful sound and big, pumping bass, this karaoke speaker can fill the room with beats. The built-in battery lets you rock the party outdoors for up to 14 hours play time on a single charge.

Party light effects

Get everyone up and dancing with party light effects! A ring of colored lights on the speaker pulses in time to the music, and there are four different lighting modes to choose from. However you love to party, this speaker has you covered.

Mic and guitar inputs


A mic input (6.3 mm) lets you take the party up a notch. There's also a guitar input, so you can take the lead vocals while you're shredding a solo! Both guitar and mic have their own volume controls on the speaker. You can change your voice, fade vocals, and add echo effects too.

All your tunes. Bluetooth

Stream playlists via Bluetooth. Plug in other sources via audio-in or USB—or plug the speaker into another speaker or amp using the line-out socket. Rotary knobs on the speaker let you select the source or even fine-tune the bass and treble.

Ready for anything

The built-in carry handle and battery means you can play wherever you like. Take the beats to a friend's house. Set up on the basketball court. You can skip tracks and turn the volume up directly from the speaker.



Issue date 2022-11-02

Version: 5.1.2

12 NC: 8670 001 76098
UPC: 8 40063 20188 0

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com