

LAPTOPS

Thin GF63

THIN GF63 12UC-823US

Specification

| Manufacturer Part # | THINGF6312823 |
|----------------------------|---|
| os | Windows 11 Home |
| | (MSI recommends Windows 11 Pro for business) |
| СРИ | Intel® Core™ i7-12650H 6+4Core |
| CPU Speed | 1.7-4.7GHz |
| Chipset | |
| Color | Black |
| Screen Size | 15.6" FHD, IPS-Level 144Hz 45% NTSC |
| Resolution | 1920x1080 |
| | <u>16:9</u> |
| GPU | NVIDIA® GeForce RTX™ 3050 Laptop GPU |
| Video Memory | 4G GDDR6 |
| Keyboard | Red keyboard with Anti-Ghost key (99 Key) |
| Speaker | 2x Speakers 2W |
| Memory | 16GB (8G*2) DDR4 3200MHz |
| UDD Compains | 512GB NVMe SSD |
| HDD Capacity HDD Interface | NVMe |
| LAN | Gb LAN |
| WLAN | |
| | Intel Wi-Fi 6 AX201(2*2 ax) |
| Bluetooth | BT 5.2 |
| Card Reader | |
| Webcam | 720p HD Webcam |
| USB | 2x USB 3.2 Gen1 |
| Type-C Port | 1x USB 3.2 Gen1 w/DP1.4 |
| Video Port | HDMI 4K @ 30Hz |
| Audio Port | 1 Mic in/ 1 headphone out |
| AC Power Adaptor | 120W |
| Battery Pack | 3 cell , 51Whr Li-Polymer |
| Dimension | 14.13"x9.99"x0.85" |
| Weight | 4.10 lbs |
| Manufacturer Warranty | 1 year Limited warranty (Include 1 Year Global) |