

4XEM 25W USB-C Charging Kit for Smartphones and USB-C Compatible Devices - Black

4XEM Part- 4X25WCHARGEKIT3B



For your convenience, 4XEM has put together this all-in-one USB-C charging kit. Designed to provide efficient and safe charging, this kit ensures that your devices stay powered up whenever you need them. With a sleek and compact design, the 4XEM 25W USB-C PD Charger is perfect for home, office, or travel use. Its USB Type-C charging port offers a universal solution, making it compatible with a wide range of devices. The kit also includes a high-quality 3ft/1m USB-C to USB-C cable, allowing for easy and seamless connectivity between your devices and the charger. The USB 3.2 Gen 2 cable supports a data transfer rate of 10Gbps, ensuring quick and efficient file transfers. With a total power budget of 25W and Power Delivery technology, the 4XEM USB-C Charging Kit provides optimized charging for your devices. The power delivery pairs perfectly with the cable which is E-marked for 100W power delivery. Order the 4XEM 25W USB-C Charging Kit today and enjoy fast, efficient, and safe charging for your devices. Stay powered up and connected wherever you go!

**4XEM Products Are Available At Your Favorite Online Retailers**

**WWW.4XEM.COM**

Contact Todd Schaus 4XEM sales Rep  
1-866-999-4936 Ext.104 [tschaus@4xem.com](mailto:tschaus@4xem.com)



## Features

### USB-C 25W Fast Charging, Quick Charge 3.0 Wall Charger Features:


- 4XEM 25W PD USB-C Charger:
- 1x USB Type-C Female charging port
- 25W total power budget
- 25W Max Power Delivery
- CE certified
- Standard NA wall charger with non-retractable prongs
- Color: Black

### 4XEM 3FT/1M USB-C TO USB-C CABLE M/M USB 3.1 GEN 2 10GBPS:

- 10 Gbps data transfer rates
- E-marked for 100W power delivery
- Meets USB 3.2 Gen 2 industry standards
- USB-C to USB-C male connectors
- Bidirectional use (no designated input or output end)
- Supports video (source and display must support DP Alt Mode)
- 3FT in length
- Color: Black



Reversible USB Type C Connectors



### Application

- Phone Calls
- At Home
- At the Office
- Travel

**4XEM Products Are Available At Your Favorite Online Retailers**



|                          |                              |   |
|--------------------------|------------------------------|---|
| Warranty Information     | Warranty                     | 1 year  |
| Connector(s)             | Charging Port                | USB Type-C  |
|                          | Power Source                 | Non-Polarized NEMA 1-15P (Standard NA Wall Outlet)<br>Fixed with Non-Retractable Prongs   |
|                          | Charging Cable Connector A   | USB Type-C Male   |
|                          | Charging Cable Connector B   | USB Type-C Male   |
|                          | Operating Mode               | Passive   |
|                          | Direction                    | Bidirectional   |
| Performance              | Industry Standards (Cable)   | USB 3.2 Gen 2   |
|                          | Charging Protocols (Charger) | FCP (5V, 9V, 12V)<br>AFC (5V, 9V)<br>QC3+ (5V, 9V, 3.6-9V)<br>USB-PD 3.0 (25W, PPS, QC4+)<br>Apple 2.4A   |
|                          | Cable Data Transfer Rate     | 10Gbps  |
|                          | E-Marker                     | 20V, 5A (100W)  |
|                          | Certifications               | CE (Charger)  |
|                          | Charger Color                | Black   |
| Physical Characteristics | Display                      | No  |
|                          | LED Indicator(s)             | None  |
|                          | Charger Height               | 1.03 in [26.2 mm]   |
|                          | Charger Width                | 1.65 in [42.0 mm]   |
|                          | Charger Length               | 2.00 in [50.7 mm]   |
|                          | Charger Weight               | 2.65 in [67.2 mm] (with power prongs)<br>2.33 oz [40 g]   |
|                          | Charging Cable Color         | Black   |
|                          | Charging Cable Length        | 3.28 ft [1.00 m]  |
|                          | Charging Cable OD            | 0.18 in [4.50 mm]   |
|                          | Charging Cable Weight        | 1.13 oz [32 g]  |
| Power                    | Total Power Budget           | 25W   |
|                          | Power Delivery               | 25W Max   |
|                          | Input Voltage                | 100-240VAC, 50Hz-60Hz @ 0.7A  |
|                          | Output Voltage (PD)          | 25W: 5V 3A, 9V 2.77A<br>25W PPS: 3.3V-5.9V 3A, 3.3V-11V 2.25A   |
| Environmental            | Operating Temperature        | 0 to 40°C (32 to 104°F)   |
|                          | Storage Temperature          | -20 to 80°C (-4 to 176°F)   |
|                          | Humidity                     | 5% to 90% (non-condensing)  |
| Packaging Information    | Package Type                 | Poly-bag  |
|                          | Package Height               | 7.09 in [180 mm]  |
|                          | Package Width                | 4.72 in [120 mm]  |
|                          | Package Length               | 0.54 in [13.7 mm]   |
|                          | Shipping (Package) Weight    | 2.72 oz [77 g]  |
| What's in the Box        | Included in Package          | 1x 25W USB-C PD Charger<br>1x 3ft/1m USB-C/USB-C Cable  |
| Notes                    | Notes                        | Cable does support video, however, connected video source equipment and display must both support DisplayPort Alt-Mode for functional A/V transmission. |

\* Product appearance and specifications are subject to change without notice.

\* Same day shipping is only available for orders shipping within the United States.

