

# Product data sheet

Specifications



## APC NetShelter Soundproof, 17U, Server Rack Enclosure, 120V, Maple

AR4017A

### Overview

Lead time Usually Ships within 2 Weeks

### Main

Product or Component Type Rack enclosure

Number of rack unit 17U

Cable length 11.98 ft (3.65 m)

Number of cables 1

### Physical

Height 39.57 in (1005 mm)

Width 29.53 in (750 mm)

Depth 44.50 in (1130.4 mm)

Product Weight 317.47 lb(US) (144 kg)

Color Maple

Mounting preference No preference

Mounting Mode Not rack-mountable

Mounting position Horizontal

Maximum Mounting Depth 2.72 ft (0.83 m)

Minimum Mounting Depth 2.26 ft (0.69 m)

Rack Width 19"

### Output

PDU Type Basic

### Conformance

Standards EIA-310D

### Ordering and shipping details

GTIN 731304621737

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	44.09 in (112 cm)
Package 1 Width	32.28 in (82 cm)
Package 1 Length	47.24 in (120 cm)
Package 1 Weight	273.81 lb(US) (124.2 kg)

## Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

## Contractual warranty

Warranty	2 Years
----------	---------

## Recommended replacement(s)