



Poly Blackwire 3315 USB-A Headset TAA (8M3U1AA)

Overview

Style, comfort and audio quality

Built for style with a sleek design that focuses on comfort and reliability. Poly signature audio quality so you know you will sound great. And intuitive and simple features so every user can connect to their preferred device simply and easily.

Connect quickly and easily

The Blackwire 3300 Series is completely plug-n-play with USB devices, so users can take calls in the office or on the go. Its robust design delivers reliability you can count on. This is the hassle-free headset you've been looking for.

Look good, feel good, sound amazing

You wear a headset all day long — better pick one that looks, feels, and sounds great. Boost your on-the-call confidence with professional-quality audio and a customized fit with a headset that can connect to your devices quickly and easily and is ready to go with you wherever you go.

Features

High-quality audio

Makes collaboration easy with Poly signature audio quality and reliability.

Headset flexibility

With professional voice quality and a customized fit, this fully adjustable headset has 180-degree pivoting speakers and a flexible microphone boom.

Connectivity

Select the right option for your device: USB-A or USB Type-C® for PC and 3.5 mm for mobile connectivity with select models.

Wearing Style

Monaural wearing style for those who prefer to leave one ear open.

Long-lasting comfort

Supports long-wearing comfort with a plush, padded headband and pillow soft ear cushions.

Optimized for communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.^[1]

[1] Visit <https://www.poly.com/us/en/products/headsets/blackwire/blackwire-3300> for more detail.

Additional specifications

Acoustic protection technology	SoundGuard ^[1]
Audio	Noise and echo reduction; Dynamic EQ optimized
Boom mic length (ft)	0.44 ft
Boom mic length (mm)	135 mm
Boom mic rotation	280°
Button user controls	Call answer/end; Mute; Volume +/-
Cable length	66.5 cm (inline module to headset); 90 cm (USB to inline module); 215 cm (total USB to headset)
Cable length (imperial)	3.85 ft (inline module to headset); 2.95 ft (USB to inline module); 7.05 ft (total USB to headset)
Color	Black
Compatibility	Compatible with PCs via USB/USB Type-C®, connects to mobile devices and tablets via 3.5 mm (BW3315/BW3325) and devices that support USB Type-C®
Compatible Operating Systems	Windows 10; macOS
Connection type	Wired USB Type-A; 3.5 mm audio
Ear cushions	Artificial leather (surface material)
Headphone type	On-ear (monoaural)
Impedance	32 ohm
Management Software	Plantronics Hub (desktop)
Manufacturer Warranty	Poly standard two-year limited warranty
Microphone bandwidth	100 Hz to 10 kHz
Microphone type	Omnidirectional
Minimum System Requirements	USB Type-A port; 3.5 mm audio
Nominal sound pressure level	118 dB SPL
Sensitivity (microphone)	-38 +/-3 dB
Sensitivity (speaker)	116 dB
Signal-to-noise ratio	>118 dB
Speaker size	14.2 mm
Special features	UC certified
UNSPSC code	43191638
UPC number	197497914559
What's in the box	Headset; User guide

[1] Protects against Acoustic Shock by limiting sounds to below 118 dBA.

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 12, 2023 3:20 PM UTC+0000