

Protect It! 10-Outlet Surge Protector with Swivel Light Bars - 5-15R Outlets, 2 USB Ports, 6 ft. (1.8 m) Cord, 1350 Joules, Black

MODEL NUMBER: TLP1006USB











Protects your lab equipment, industrial tools and other electronics against power surges, spikes and line noise.

Features

10-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home, office, retail or industrial workstation, this Protect It!® surge protector features a 1350 joule rating to defend your valuable electronic components against damaging power surges and spikes. The six-foot (1.8-meter) AC input cord with NEMA 5-15P plug gives you some flexibility in placing the surge protector away from the nearest wall outlet.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, wireless router, power tools, laboratory equipment and other home/office/industrial electronics into 10 NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. The outlets are adequately spaced apart to accommodate bulky transformers without blocking adjacent receptacles.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Swivel Light Bars Brighten Your Workspace

Two adjustable light bars, each with 1000 lumens (20W), provide bright white light to illuminate any dark corners.

USB Charger Offers Easy Access to Mobile Devices

Two USB-A ports share 2.4A for charging your smartphone, tablet and other USB mobile devices.

Includes the Latest Safety Features to Maintain Your Equipment's Well-Being

Two lighted on/off switches allow easy one-touch control over the light bars and all equipment connected to the surge protector. Integrated 15A resettable circuit breakers help prevent equipment damage due to overloads. Diagnostic LEDs let you know that the wall outlet is grounded and that your equipment is protected.

Highlights

- 10 NEMA 5-15R outlets distribute AC power to connected home/office/work equipment
- 1350 joules protect your valuable electronics against dangerous surges and spikes
- Swivel LED light bars provide 1000 lumens each to illuminate dark corners
- 6 ft. input cord allows some flexibility in placing devices away from wall outlet
- On/off switches give you onetouch control over lights and connected equipment

Package Includes

- TLP1006USB 10-Outlet Surge Protector, Black
- Owner's manual



Flexible Installation Options

Place the TLP1006USB on any flat surface in your home, office, workbench or anywhere else you need power for your equipment. Integrated rear keyhole slots accommodate wall or desktop mounting.

Specifications

OVERVIEW		
UPC Code	037332283269	
Product Type	Surge Protector	
Charging Form Factor	Strip	
Device Compatibility	Phone; Tablet; Amazon Kindle	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Details	SJT	
Input Cord Length (ft.)	6	
Right-Angle Plug	No	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
ОИТРИТ		
Frequency Compatibility	60 Hz	
Output Receptacles	(10) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(10) Yes	
Outlet Orientation	Single row of outlets	
Right-Angle Outlets	Yes	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Switches	Combination AC circuit breaker and 2 position on/off power switch	
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status, "grouded status (red)	



Total Charging Watts 1.	2.4A	
Total Charging Amps 2 Total Charging Watts 1.	2.4A	
Total Charging Watts 1.		
	12	
	12	
Charging Method U	USB	
Charging Port Type (2	(2) USB A (FEMALE)	
Charging Ports / Amps (2	(2) 2.4A	
Overcharge Protection N	No	
Charging Amps per Port 2	2.4A	
LIGHTING		
Number of Light bars 2	2	
Light bar Color B	Bright White	
Light bar Brightness 1	1000 lumens (20W)	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating 1	1350	
AC Suppression Response Time <	< 1 ns	
Protection Modes Ir	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
UL1449 Let Through Rating 6	600V	
EMI / RFI Filtering Y	Yes 150KHz - 100MHz	
Automatic Shut-Off N	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Material of Construction P	Plastic	
Power Cord Color B	Black	
Housing Color B	Black	
Mounting Holes or Slots Y	Yes	
Receptacle Color Y	Yellow	
Shipping Dimensions (hwd / in.) 2	26.20 x 5.60 x 2.40	
Shipping Dimensions (hwd / cm) 6	66.55 x 14.22 x 6.10	



Shipping Weight (lbs.)	3.26
Shipping Weight (kg)	1.48
Unit Dimensions (hwd / in.)	24.400 x 5.500 x 2.040
Unit Dimensions (hwd / cm)	62 x 14 x 5.2
Unit Weight (lbs.)	2.84
Unit Weight (kg)	1.29
Input Cord Color	Black
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed
Product Compliance	FCC Part 15 Class B (USA); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.