

These small office, black & white, multifunction laser printers with ADF (Automatic Document Feeders) produce exceptional quality outputs at fast speeds of up to
42 pages per minute<sup>2</sup>, with your first print in your hands in less than 4.9 seconds.

# imageCLASS MF462dw

# imageCLASS MF465dw

| Print Speeds                                    | Up to 37 pages per minute   | Up to 42 pages per minute |
|---|---|---------------------------|
| Functions                                       | Print, Copy, Scan, Fax  |                           |
| Connectivity                                    | WiFi <sup>3</sup> , USB, Ethernet, USB Flash Drive  |                           |
| Auto 2-Sided Print, Copy<br>and Scan Capability | Yes   |                           |
| High Capacity Paper Trays                       | 250 Sheet Cassette, 100 Sheet Multipurpose Tray,<br>and Optional 550 Sheet Cassette             |                           |
| 2-Sided Auto Document<br>Feeder (One Pass Scan) | Up to 50 sheets of letter-sized plain paper   |                           |
| Black Toner Cartridge<br>Options                | Standard Cartridge 070 (up to 3,000 pages),<br>High Volume Cartridge 070 H (up to 10,200 pages) |                           |
| Control Panel                                   | Customizable 5-Inch Touchscreen LCD Panel   |                           |
| Printer Size (closed) (WxLxH)                   | 16.6" × 18.1" × 14.8"   |                           |

۲

# **Everything you need in a B&W laser printer; usability, reliability and efficiency.**



# Fast Print Speed<sup>2</sup>

Print up to 42 pages-per-minute (MF465dw) / 37 pages-per-minute (MF462dw) with your first print out in approximately 4.9 seconds (letter).





# **Mobile Connectivity**<sup>4</sup>

Print on-the-go with Canon PRINT Business, Apple® AirPrint® and Mopria<sup>™</sup> Print Service.





**50 Sheet, 2-Sided Auto Document Feeder** (One Pass Scan)

Scan multi-page documents easily with the auto document feeder up to 50-sheets.

# Application Library & Cloud Connectivity

Easily access the features you use the most with Application Library. Application Library's Cloud App feature also supports cloud storage directly from an external webpage. Print or scan<sup>5</sup> documents directly to or from DropBox, Google Drive, or OneDrive.



#### Easliy navigate all the features through adjustable 5 inch touch LCD screen

**Customizable 5-Inch** 

**Touchscreen LCD** 



These printers can hold up to 250 sheets in built-in paper cassette, 100 sheets in multipurpose tray, and 550 sheets in optional paper tray



( )

# High Volume Printing

Print up to 3,000 pages with replacement Toner 070 or up to 10,200 pages with High Capacity Toner 070 H.



USB Flash Drive Port Print files directly from

USB Flash Drives after attaching to port.



# **Support and Service**

Canon U.S.A. takes pride in delivering complete customer satisfaction. Canon's friendly and knowledgeable Customer Service Team provides expert assistance for every level of experience, offering the support, peace of mind, and value your business deserves.<sup>6</sup> These printers come with a three-year limited warranty.<sup>1</sup>



۲

۲

# **SPECIFICATIONS**

### Main Unit

#### Core Functions (Standard)

Print, Copy, Scan, Fax MF462dw: MF465dw: Print, Copy, Scan, Fax Item Code MF462dw: 5951C015 5951C005

MF465dw Processor

### Canon Custom Processor

**Control Panel** 5 inch Touch LCD MF462dw: MF465dw 5 inch Touch LCD

Memory 1GB

Standard Interface Connection

USB 2.0 High-Speed, 100Base-TX/10Base-T(IEEE 802.3 compliant), Wi-Fi (IEEE 802.11b/g/n)<sup>3</sup>

Paper Capacity (Letter, 20 lb. Bond) Standard: 250 sheets Paper Cassette 100 sheets Multipurpose Tray

Paper Output Capacity (Letter, 20 lb. Bond) Standard 150 sheets

#### Supported Media Types

Thin, Plain, Recycled, Thick, Bond Cassettes: Multipurpose Tray: Thin, Plain, Recycled, Thick, Bond, Label, Envelope

#### Supported Media Sizes

Cassettes: Letter, Legal, Statement, Executive Custom (Min. 4.1" x 5.8" to Max. 8.5" x 14") Multipurpose Tray: Letter, Legal, Statement, Executive Envelope: COM10, Monarch, C5, DL Custom (Min. 3" x 5" to Max. 8.5" x 14")

#### Supported Media Weights

Cassettes: 16 lb. Bond to 32 lb. Bond (60 to 120 g/m2) Multipurpose Tray: 16 lb. Bond to 43 lb. Bond (60 to 163 g/m2)

Warm-up Time 14 sec or less

 $( \blacklozenge )$ 

Dimensions (W x D x H) Standard (Desktop): 16.6" x 18.1" x 14.8"

### Box Dimensions (W x D x H) Box: 22.4" x 21.5" x 20.6"

Weight<sup>7</sup> Unit: Approx. 34.4 lb Boxed Weight: Approx. 48.5 lb.

**Operating System** 

Windows\*10/Windows\*11/Windows\*Server2012/ Windows\*Server2012 R2/Windows\*Server2016/ Windows\*Server2019/Windows\*Server2022 macOS 10.13 (or later)

### Print Specifications

**Printing Method** Laser Beam Printing Print Speed<sup>2</sup>

MF462dw: Up to 37ppm (Letter) MF465dw: Up to 42ppm (Letter) First-Print-Out Time Approx. 4.9 Seconds Recommended Monthly Page Volume 750 to 4,000 Pages

Duty Cycle Up to 80,000 Print Resolution (dpi) Up to Up to 1200dpi x 1200dpi Standard Page Description Languages UFR II. PS. PC

#### **Double-Sided Printing**

Automatic (Standard) **Direct Print** Yes (USB) Printing from Mobile and Cloud-based Services<sup>4, 5</sup> Apple® AirPrint,® Canon PRINT Business, Mopria<sup>™</sup> Print Service

۲

## Copy Specifications

#### Copy Speed

Single sided (LTR): Up to 37 ppm Double sided (LTR): Up to 31.5 ipm MF462dw: MF465dw: Single sided (LTR): Up to 42 ppm Double sided (LTR): Up to 35.1 ipm

First-Copy-Out Time (Letter) 6.0 seconds

Copy Resolution (dpi) Up to 600dpi x 600dpi Copy Size

Platen: Up to Letter/A4 ADF: Up to Legal Multiple Copies

Up to 999 Copies

Magnification 25% - 400% (1% Increments)

Copy Features Single-Pass Duplexing Automatic Document Feeder

## Scan Specifications

Type

Single-Pass Duplexing Automatic Document Feeder Document Feeder Paper Capacity 50 Sheets (20 lb. Bond)

**Document Feeder Supported Media Sizes** Letter, Legal \*Width Custom sizes (Min. 5.8"-Max.8.5") **Document Feeder Supported Media Weights** 

13-28 lb. Bond (50-105 g/m2)

Platen Acceptable Originals Sheet, Book

Pull Scan ScanGear MF for TWAIN, and WIA

Scan Resolution (dpi) Up to 600 x 600 dpi

Scan-to-Mobile Devices E-mail, PC, USB memory, FTP, Cloud, iFAX

Scan Speed (Letter) Single-sided:50/40 ipm (BW/Color) Double-sided: 100/80 ipm (BW/Color)

### **Fax Specifications**

Modem Speed Super G3: 33.6 kbps G3: 14.4 kbps **Compression Method** MH, MR, MMR, JBIG Resolution (dpi) 400 x 400, 200 x 400, 200 x 200, 200 x 100 Sending/Recording Size Statement to Legal

Fax Memory Up to 512 pages Speed Dials Max. 281 Group Dials/Destinations

Max. 299

# imageCLASS MF462dw / MF465dw

#### Sequential Broadcast

Max. 310 Addresses

Memory Backup Yes

#### **Fax Features**

Sending 2-Sided Document, Printing Received Data 2-Sided, Sender's Name (TTI), Direct Send, Preview, TX Report, Sequential Broadcasting

## Security Specifications

Authentication

Department ID

## Network

TLS1.3, IPSec support, IEEE 802.1X authentication, SN-MPv3, IP Address Filtering, Configure ON/OFF settings for network application functions, Job Log Conceal Function, Restricted access to the printer's storage media, Verify System at Startup

#### Document

SecurePrint, Device Signature PDF/XPS, Restricted E-mail/File send functions, Confirming FAX number, Restrict Fax Driver Transmissions, Restrict Sending from History

#### Wi-Fi Authentication Methods

Wi-Fi Infrastructure Mode: 128(104)/64(40)bit WEP WPA-PSK(TKIP/AES-CCMP) WPA2-PSK(TKIP/AES-CCMP) WPA-EAP(AES-CCMP) WPA2-EAP(AES-CCMP) WPA2-PSK(AES-CCMP)

Wi-Fi Access Point:

# **Environmental Specifications**

#### **Operating Environment**

50 to 86 °F Temperature: Humidity: 20 to 80% RH (no condensation) Power Requirements

AC 120-127 V 60 Hz 6.0A

### **Power Consumption**

Maximum: Approx. 1250W Approx. 8W Standby: Approx. 0.1 W Sleep Mode: Typical Electricity Consumption (TEC) Rating: 0.33 kWh Standards ENERGY STAR® Qualified, Rated EPEAT<sup>8</sup> Silver

# What's in the Box (MF462dw):


- MF462dw Product
  - Cartridge 070 Black Standard, Approx.
  - 3,000 Page Yield
- Power Cord
- Telephone Cable User Software DVD-ROM
- Documentation

## What's in the Box (MF465dw):

- MF465dw Product
- Cartridge 070 Black Standard, Approx.
- 3,000 Page Yield
- Power Cord • Telephone Cable
- User Software DVD-ROM
- Documentation

# CONFIGURATION AND ACCESSORIES

# imageCLASS MF462dw / MF465dw



۲

<sup>1</sup> Warranty program is subject to certain conditions and restrictions. See warranty card for details.

- <sup>2</sup> Print speed is based on internal testing. Print speed may vary, depending on the number of copies selected as well as the settings for size, type, and orientation of paper
- <sup>3</sup> Wireless printing requires a working network with wireless 802.11b/g or 802.11n capability. Wireless performance may vary based on terrain and distance between the printer and wireless network clients.
- <sup>4</sup> Canon PRINT Business is a free app available on the App Store<sup>®</sup> and Google Play<sup>™</sup> Store. For more information, including compatibility, please visit https://www.usa.canon.com/mobile-app. Please see the respective websites for Apple AirPrint and Mopria Print Service for compatibility and additional information <sup>5</sup> Subscription to a third-party cloud service is required and subject to third party terms and conditions.
- <sup>6</sup> Replacement model may be new or refurbished quality.
- 7 Includes consumables.

( )

<sup>8</sup> For latest EPEAT ratings (Gold/Silver/Bronze), please visit HYPERLINK "http://www.epeat.net" www.epeat.net.





As an ENERGY STAR partner, Canon U.S.A., Inc. has qualified these models as meeting the ENERGY STAR energy efficiency criteria through an EPA recognized certification body. ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. Canon, imageCLASS, and the GENUINE logo are registered trademarks of Canon Inc. in the United States and may also be registered trademarks or trademarks in other countries. Wi-Fi is a registered trademark of the Wi-Fi Alliance. Android and Google Play are trademarks of Google Inc. iPad, iPhone, iPod touch, Mac, and the App Store are trademarks of Apple Inc., registered in the United States and/or other countries. AirPrint and the AirPrint logo are trademarks of Apple Inc. Mopria and the Mopria logo are trademarks of the Mopria Alliance, Inc. Windows and Windows Server are trademarks of Microsoft Inc. in the United States and/or other countries. All other referenced product names and marks are trademarks of the accurity of the countries and/or other countries. The accurity for the countries and/or other countries. All other referenced product names and marks are trademarks of the accurity of the countries and the trademarks of the trademarks of the accurity of the counter of the countries. All other referenced product names and marks are trademarks of the accurity of the counter of the counter of the countries. All other referenced product names and marks are trademarks of the accurity of the counter of th tive owners. Canon products offer certain security features, yet many variables can impact the security of your devices and data. Canon does not warrant that use of these features will prevent security issues. Nothing herein should be construed as legal or regulatory advice concerning applicable laws; customers must have their own qualified counsel determine the feasibility of a solution as it relates to regulatory and statutory compliance. Specifications and availability subject to change without notice. Not responsible for typographical errors. ©2023 Canon U.S.A., Inc. All rights reserved.

Final ME462 465 Brochure #1 indd 4

7/14/23 12:53 PM

۲

۲