

## ZH400ST

Eco-friendly high brightness short throw Full HD laser projector









- Bright Full HD 1080p DuraCore laser projector -4000 lumens and IP6X certified
- Compact and short throw lens for easy installation
  360-degree and portrait projection
- Reduced power consumption for a long life span -DuraCore laser technology delivers 30,000 hours maintenance free laser light source
- External power supply More reliability, portability and energy efficiency



The ZH400ST is one of Optoma's most compact and hassle-free Full HD 1080p DuraCore laser projectors to date. Designed for maintenance-free continuous operation, this 4000-lumen projector delivers powerful image performance with flexible installation features and extensive connectivity options in a sleek, compact form factor, up to 34% smaller than previous Optoma models.<sup>1</sup>

An added benefit, the ZH400ST features an external power supply offering more reliability, portability and energy efficiency.

## **Specifications**

The following specifications are preliminary and subject to change without notice

Display/image

DI P™ Display technology

Resolution 1080p Full HD (1920x1080)

Brightness 4,000 lumens Contrast ratio 300,000:1 2 000 000:1 Contrast ratio - dynamic Native aspect ratio 16:9 Aspect ratio - compatible 4:3,16:9,16:10 Keystone correction -+/-30°

horizontal

Keystone correction - vertical +/-30° 1073.4 Displayable colours (millions) 15 ~ 140Khz Horizontal scan rate Vertical scan rate 24 ~ 120Hz Uniformity 75%

0.91m ~ 7.42m (36" ~ 292") diagonal Screen size

Lamp info Light source type

Laser LASER life 30,000 hours

Optical

Throw ratio 0.496:1

Projection distance 0.4m - 3.2m / 15.75" - 125.98"

Zoom type Fixed Focal length 7.51 Native offset 116%

Connectivity Connections

Inputs 2 x HDMI 2.0

Outputs 1 x Audio 3.5mm, 1 x USB-A power 1.5A

Control 1 x RS232, 1 x RJ45

General

Noise level (typical) 32dB Noise level (max) 34dB

PC compatibility FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac NTSC M/J, 3.58MHz, 4.43MHz PAL B/D/G/H/I/M/N, 4,43MHz 2D compatibility

SECAM B/D/G/K/K1/L, 4.25/4.4MHz 480i/p, 576i/p, 720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz)

3D compatibility Yes (DLP 3D; PC frame sequential 120Hz 3D, Blu-ray DVD

3D)ver-Under: 1080p24, 720p50 / 60

3D Full 3D

Security Security bar, Kensington Lock, Password protected interface IP6X IP rating

25 languages: Arabic, Czech, Danish, Dutch, English, Farsi, Finnish, French, German, Greek, Hungarian, Indonesian, Italian, OSD / display languages

Japanese, Norwegian, Polish, Portuguese, Romanian, Russian, Chinese (simplified), Spanish, Swedish, Chinese (traditional),

Turkish, Vietnamese

24/7 operation Yes 360° operation Yes

Operating conditions 0°C ~ 40°C, Max. Humidity 80%, Max. Altitude 2,500m

Remote control Card style Speaker count Watts per speaker 15W In the box AC power cord

Remote Control with CR2025 Battery

Basic user manua

Optional wireless models QuickCast Pro 4K KIT Power

External power supply, 100V ~ 240V, 50-60Hz Power supply Power consumption (standby) <0.5W Power consumption (min) 119W Power consumption (max) 173W

Weight and dimensions

Dimensions (W x D x H) 10.79" x 8.5" x 4.49" Gross weight 9.26 lbs Net weight 6.61 lbs UPC 796435 44 713 7

