

PERFORMANCE

Display Size

34.14"

View Area

799.8x334.8 mm

Panel

In-Plane Switching

Backlight

WLED

Aspect Ratio

21:9

Resolution

3440x1440

Pixel Pitch

0.2325x0.2325 mm

Dot / Pixel Per Inch

109 dpi

View Angle (H / V)

178° / 178°

Response Time

4ms (Extreme mode) / 6ms (Typical mode)

Color Support

1.07 Billion

Refresh Rate

60Hz

Brightness

300 cd/m²

Contrast Ratio

1000:1

Color Gamut

99% sRGB

Screen Surface Treatment

Anti-glare

Curvature

3800R

Camera

ThinkVision® MC 50 Support

Microphone

None

Speakers

3Wx2

Power Consumption (Typical / Maximum)

36W / 230W

Power Adapter

Integrated

Touchscreen

None

Smart System

None

DESIGN

Stand

Tilt, Swivel, Height Adjust Stand

Case Color

Raven Black

Side Bezel Width

9.5 mm

Dimensions with Stand (HxWxD)

621.4x817.3x245 mm / 24.46x32.18x9.65 inches

Weight (Including Stand)

10.8 kg / 23.8 lbs.

Mounting

Supports VESA mount 100mm

ThinkCentre® M Series Support

Tiny, Nano Support

CONNECTIVITY

USB Port

3x USB 3.2 Gen 1 (downstream), 1x USB-C® 3.2 Gen 1 (downstream), 1x USB-C 3.2 Gen 1 (1x DP 1.2 Alt Mode, upstream), 1x USB-B 3.2 Gen 1 (upstream)

Video Connector

2x HDMI® 2.0, 1x DP 1.2, 1x DP Out, 1x USB-C 3.2 Gen 1 (DP 1.2 Alt Mode)

Network Connectivity

1x RJ45, Ethernet (10M/100M/1000M)

SERVICE

Base Warranty

3-year

CERTIFICATIONS

Environmental Certification

ENERGY STAR® Certified, TCO 9.0, EPEAT™ Gold, RoHS

Ergonomic Certification

Eyesafe® Display, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Low Blue Light, TÜV Rheinland Flicker Free, TÜV Rheinland Eye Comfort

Sync Technology

None

Special Features

- Factory Calibration: Avg. Delta E<2
- Picture In Picture (PIP) / Picture By Picture (PBP) Support
- HDR Compliance
- DaisyChain Support (DP out)
- KVM Switch
- Lenovo® ThinkColour (Lenovo Display Control Center) Support
ThinkColour can only be used with Windows® 10 and Windows 11
- Smart Power
The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device

SOFTWARE

Operating System

Support Windows 10, Windows 11

ACCESSORIES

Video Cables

USB Type-C® cable

MODEL

Announce Date : 2023-07-24

EAN / UPC : 0197532306653 / 197532306653 / None

JAN



Product image is a sample, it may not match the real color of this model

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference