



8GB DDR5 PC5-38400 - 4800Mhz DIMM Notebook Memory Module - V7384008GBD-U

V7384008GBD-U

SKU: HH3900

V7 DDR5 has been designed to meet increasing needs for high performance and power efficient memory in a wide range of applications from client systems to high performance server platforms. DDR5 is designed to support scaling memory performance without degrading channel efficiency at higher speeds and has double the burst length and 32banks allowing for increased module capacity. Decision feedback equalization enables IO speed scalability for higher bandwidth and improved performance. DDR5 supports double the bandwidth compared to DDR4 and starts at speeds of 4800Mhz which is a considerable increase on the highest DDR4 speeds.

- JEDEC industry standard specification
- Improve System Performance
- Guaranteed Compatibility
- TAA Compliant
- Easy to install

General

Sku: HH3900
 Model: V7384008GBD-U
 EAN: 5050914227692
 Warranty: Lifetime
 Compliance: CE, RoHS
 Country Of Origin: Taiwan
 Package Type: Blister
 SAP: 5845377

Package Dimensions

Package Dimensions (L/W/H): 170 x 55 x 15 mm
 Package Weight: 30g

Product Dimensions

Product Dim (L/W/H): 170 x 55 x 15 mm
 Product Weight: 30g

Technical

Rank: Single
 Buffering: Non-ECC, Unbuffered DIMM
 Platform: Notebook
 RAM Type: DDR5
 Clock Rate: 4800 Mhz
 Capacity: 8 GB
 Memory Form Factor: 288PIN DIMM
 Memory Module: PC5-38400 - 4800Mhz CL40