



## 32GB DDR5 PC5-38400 - 4800Mhz SO DIMM Notebook Memory Module - V73840032GBS-U

### V73840032GBS-U

SKU: HH3902

V7 DDR5 has been designed to meet increasing needs for high performance and power efficient memory in a wide range of applications from client systems to high performance server platforms. DDR5 is designed to support scaling memory performance without degrading channel efficiency at higher speeds and has double the burst length and 32banks allowing for increased module capacity. Decision feedback equalization enables IO speed scalability for higher bandwidth and improved performance. DDR5 supports double the bandwidth compared to DDR4 and starts at speeds of 4800Mhz which is a considerable increase on the highest DDR4 speeds.

- JEDEC industry standard specification
- Improve System Performance
- Guaranteed Compatibility
- TAA Compliant
- Easy to install

#### General

SkU: HH3902  
 Model: V73840032GBS-U  
 EAN: 5050914227647  
 Warranty: Lifetime  
 Compliance: CE, RoHS  
 Country Of Origin: Taiwan  
 Package Type: Blister  
 SAP: 5845376

#### Package Dimensions

Package Dimensions (L/W/H): 170 x 55 x 15 mm  
 Package Weight: 30g

#### Product Dimensions

Product Dim (L/W/H): 170 x 55 x 15 mm  
 Product Weight: 30g

#### Technical

Rank: Single  
 Buffering: Non-ECC, Unbuffered DIMM  
 Platform: Notebook  
 RAM Type: DDR5  
 Clock Rate: 4800 Mhz  
 Capacity: 32 GB  
 Memory Form Factor: 262PIN SO-DIMM  
 Memory Module: PC5-38400 - 4800Mhz CL40