



# Poly Blackwire 3215 3.5mm Top (85R05AA)

## Overview

### Freedom to work your way

The Blackwire 3200 Series provides a quality audio experience in a headset that's built for enterprise needs. With a sleek design and flexible microphone boom for a customizable fit, what's not to love?

### Poly signature audio quality

Experience the high-quality audio you expect from Poly with a headset that offers PC wideband, a noise-canceling mic, and hi-fi stereo sound options. Dynamic EQ optimizes call quality and automatically adjusts the settings for listening to multimedia.

### Long-lasting comfort and portability

Relax while you talk knowing your headset is secure- lightweight metal headband offers durability plus a custom fit. Leatherette ear cushions fold flat for easy portability.

### Advanced connectivity

Ideal for managing calls on your PC, mobile phone, or tablet combined with the comfort and durability of a corded headset for greater flexibility.

# Features

## Enhanced call quality

Dynamic EQ optimizes the quality of your voice on calls, and automatically adjusts the EQ settings when you want high-quality sound for listening to music or for multimedia playback.

## Wearing style

Monaural wearing style for those who prefer to leave one ear open.

## Simple call management

Use the intuitive inline controls to answer/end calls, control volume, and mute to simplify call management. Conveniently placed indicator lights provide helpful but unobtrusive user call, mute, and volume status.

## Connectivity options

Enhanced connectivity for your devices: USB Type-C® cord with tethered USB-A adapter for PC and 3.5 mm for mobile or tablet connectivity

## Lightweight design

A lightweight metal headband offers durability and a comfortable custom fit.

## Optimized for communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.

## Specifications

<b>Audio</b>	Noise and echo reduction; Dynamic EQ optimized
<b>Minimum dimensions (W x D x H)</b>	15.5 x 3.2 x 17.8 cm
<b>Minimum dimensions (W x D x H)</b>	6.1 x 1.25 x 7.1 in
<b>Weight</b>	64 g
<b>Weight</b>	0.14 lb
<b>Package dimensions (W x D x H)</b>	190 x 210 x 55 mm
<b>Package weight</b>	300 g
<b>Special features</b>	UC certified
<b>Minimum System Requirements</b>	3.5 mm audio
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>What's in the box</b>	Headset (top only)

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard <sup>[1]</sup>
<b>Boom mic length (ft)</b>	0.43 ft
<b>Boom mic length (mm)</b>	130 mm
<b>Boom mic rotation</b>	270°
<b>Cable length</b>	129.5 cm
<b>Cable length (imperial)</b>	4.25 ft
<b>Cartons per layer</b>	6
<b>Cartons per pallet</b>	36
<b>Certified collaboration software</b>	Skype for Business; Avaya; Cisco Jabber
<b>Color</b>	Black
<b>Compatibility</b>	Compatible with PCs via USB/USB Type-C®, connects to mobile devices and tablets via 3.5 mm and devices that support USB Type-C®
<b>Compatible Operating Systems</b>	Windows 10; macOS
<b>Connection type</b>	3.5 mm audio
<b>Country of origin</b>	Made in China or Mexico
<b>ECCN</b>	EAR99
<b>Ear cushions</b>	Artificial leather (surface material)
<b>Ecolabels</b>	TCO Certified
<b>HTS code</b>	8518302000
<b>Headphone type</b>	On-ear (monoaural)
<b>Impedance</b>	32 ohm
<b>Management Software</b>	Plantronics Hub (desktop)
<b>Microphone bandwidth</b>	100 Hz to 10 kHz
<b>Microphone type</b>	Omnidirectional
<b>Multiple order quantity</b>	15
<b>Package dimensions (W x D x H)</b>	7.48 x 8.26 x 2.16 in
<b>Package weight</b>	0.66 lb
<b>Pallet (layers)</b>	6
<b>Pallet dimensions</b>	40 x 48 x 58.66 in
<b>Pallet dimensions (W x D x H)</b>	101.6 x 121.9 x 149 cm
<b>Pallet weight</b>	787.05 lb
<b>Pallet weight</b>	357 kg
<b>Products per pallet</b>	900

<b>Products per pallet layer</b>	150
<b>Sensitivity (microphone)</b>	-38 dBV/Pa
<b>Sensitivity (speaker)</b>	90 dB
<b>Signal-to-noise ratio</b>	>118 dB
<b>Speaker bandwidth</b>	200 Hz to 6.8 kHz (speech mode); 20 Hz to 20 kHz (media mode)
<b>Speaker size</b>	28 mm
<b>UNSPSC code</b>	43191638

---

*[1] Protects against Acoustic Shock by limiting sounds to below 118 dBA.*

---

## Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 14, 2024 6:48 PM UTC+0000