



Poly Savi 8420 Office Stereo DECT 1920-1930 MHz Headset (8L7F2AA)



Overview

Built for the modern office

Ready for the modern office with an intuitive user interface on the universal base that can connect to almost any Savi headset. Ensure flexibility for users with the ability to connect from your computer, desk phone or mobile phone [1].

Be heard clearly

With the Poly Savi 8400 Office series headset system, you can stay focused on your tasks while enjoying crystal-clear conversations thanks to a noise-canceling microphone with close conversation limiting.

Multi-device connectivity

Designed for the modern office with 3-way connectivity, the Poly Savi 8400 office series is the perfect solution for business calls allowing you to stay connected in the office. You can even conference four headsets together with the base for increased productivity.

Untether from your desk

Enjoy the convenience of hands-free calling and a longer roaming range with the Poly Savi 8400 office series. With up to 13 hours of talk time and the ability to roam up to 590 ft / 180 m means you can keep the calls going, even away from the desk [2].

Features

3-way connectivity

Manage all your calls with a compatible single base that offers 3-way connectivity – computer, desk phone and mobile.

Take it further

Everyone can move, multitask, and get more done with up to 13 hours of talk time on a single charge. Convenient voice prompts notify of mute status, wireless range limit and more.

Training made easy

Make training and collaboration easy with the ability to conference up to 4 headsets onto a single base.

Crystal-clear calls

Reduce background sounds for the person you are talking to with a noise-canceling microphone and close conversation limiting while you stay in the zone with active noise canceling.

Privacy is ensured

Privacy of your conversation is ensured: DECT™ security-certified headset.

Communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.^[3]

[1] Does not connect to the Savi 7200 headset.

[2] Line of sight from computer.

[3] Visit www.poly.com/savi-8400-office for more detail.

Additional specifications

Audio	Active noise cancellation (ANC); Noise cancellation with close conversation limiting
Base controls	Scroll wheel; Back key; USB softphone line button; Bluetooth® line button; Telephone interface line button; Configurable button
Battery life	Up to 13 hours (talk time); Up to 50 hours (standby time)
Battery type	Rechargeable Li-ion polymer
Bluetooth version	5.2
Button user controls	Power on/off; Call answer/end; Mute; Volume +/-
Charge time	3 hours
Color	Black
Compatible Operating Systems	macOS; Windows
Connection type	Bluetooth®; DECT™
Connects to	Desk phone; PC; Mobile
Ear cushions	Artificial leather (surface material)
Impedance	32 ohms
Management Software	Poly Lens
Manufacturer Warranty	Poly standard two-year limited warranty
Minimum System Requirements	USB Type-A port (PC); USB Type-C® port (PC); Bluetooth® (mobile phone); EHS interface (desk phone)
Sensitivity (microphone)	112 dB SPL
Sensitivity (speaker)	118 dB SPL
Speaker size	32 mm
Special features	Color display on office base for audio settings management
Supported bluetooth profiles	A2DP; HFP; HSP
UNSPSC code	43191638
UPC number	197497836707
What's in the box	Wireless headset; USB Type-A cable; USB Type-C® cable; Office base; AC power adapter; Charging cradle; Telephone interface cable (TIC)
Wireless range	Up to 180 m in open area; Up to 55 m in typical office environment
Wireless range (imperial)	Up to 590 ft in open area; Up to 180 ft in typical office environment

Services

Poly Services

★ : Recommended

Poly Support Services

3 year Poly+ Savi Service	PSAVI312 ★
3 year Next Business Day Hardware Advance Replacement Savi Poly DaaS Service	DSAVIDS3
3 year Partner Poly+ Savi Service	PSAVI362

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Jan 05, 2024 1:54 PM UTC+0000