

Universal HD over Coax® Digital Video Recorder DW-VA1G48xT

					Dimensions				
RTSP	WANGLAS			NO NET PAR		Unit:	Inch (m	im)	10.55" (268mm)
LOM Jnviersal HD	8 CH 240 fps 3 Channels	4K Up to 4K	PathFinder [™]	4K Ultra HD	5year Limited Warranty		ecificat	1.77" (45 mm) 14.96" (3	80mm)
over Coax®	240 Total fps	Recording		Output		· · · · · · · · · · · · · · · · · · ·			
						VIDEO Operating system Embedded Linux*			
Summary							Channel 8 channels		
VMAX® A1 G4™ is an embedded DVR that records standard analog,							Signals Supported Monitor	Standard analog signal up to 960H True HD, VGA and Spot outputs	I, HD-Analog and HD-TVI up to 4k
	nd HD-TVI fo						Frame rate	240fps	
video output. The DVR is a seamless upgrade to HD resolution for new ROI from existing coaxial infrastructure. Up the Coax (UTC) remote configuration is available with all compatible cameras. The 8-channel VMAX A1 G4 model is NDAA and TAA compliant, and is available with							Resolution	True HD: 3840×2160 (4K), 2560x14 1024x768, 800x600 VGA: 1920x1080, 1280x1024, 1024x CVBS: D1 (720x480)	
							Screen mode	1, 4, 6 and 9	
p to 32TB of				,		Audio	Input/output Codec	8 inputs/1 output ADPCM	
	-					Alarm inpu		8 inputs/2 outputs	
Features						Serial 1x RS485 User interface Graphical user interface (GUI), USB mouse			
						PERFORMANCE			
	D over Coax®	DVR recor	ds HD-Analo	g, HD-TVI a	and standard		Compression	H.265, H.264 Continuous schedules sensor-acti	vated motion detection proceed
coax up to 4K resolution Advanced H.265, H.264 Linux® embedded DVR							Recording mode	Continuous, schedules, sensor-activated, motion detection, pre and post alarm, emergency, quick backup Dual recording for live and playback 3840x2160, 2560x1944, 2560x1440, 1920x1536, 1920x1080, 1280x720	
8-channels, 240fps real-time 30fps recording						Decording	Recording resolutions	720x480, 960x480	0, 1920X1556, 1920X1080, 1280X72
Up to 4K recording resolution at 56fps (7fps per channel)						Recording		Full HD-D1 (1920x1080, 1280x720, 720x480, 960x480): 240fps (30 per channel) 3MP (1920x1536): 144fps (18fps per channel) 4MP/2K (2560x1440): 120fps (15fps per channel) 5MP (2560x1944): 96fps (12fps per channel)	
 PathFinder™ easy end-to-end remote connection with NAT Traversal (STUN/TUN) support 							Recording and playback rate		
Event camera group recording							Playback	Playback speed	x1, x2, x4, x8, x16, x32 Intelli-search by time bar, calendar (date and time), event search and
							Playback functions	thumbnail search	
 Complete system analysis with real-time system and network status monitoring 						Storage	HDD interface Maximum internal	2x SATA HDD, 1x e-SATA Up to 32TB internal storage	
0							storage HDD health check	Real-time temp alert, S.M.A.R.T. wit	h omail notifications
• Mobile Application for iOS® and Android® devices							Camera OSD	Via UTC	
 OSD and PTZ control via coax (UTC) 						Features	control Digital zoom	Live and playback	
 Signal hybrid detects the camera signal automatically 							Software upgrade	USB flash drive, network upgrade, FTP remote upgrade	
Instant channel swap, no need to disconnect or reboot the DVR							Mobile client Covert channel	Mobile app for Apple and Android Yes	devices
Snapshot Notify™: programmable interval snapshot email notifications						Transaction verification		Text-in based (USB to serial support, TCP/IP network), display POS	
4K (3840 x 2160) True HD, VGA and Spot video outputs						data on live and playback			
Up to 32TB internal storage						LAN 1,000Mbps (RJ45)			
HDD calculation and auto-recording configuration						Protocol	Web viewer	Fixed IP, DHCP, UPnP, DDNS Live, playback and configuration u	o to 10 multiple connections
			-				Video streaming	Dual stream for local recording and	I network transmission
Thumbnail search with hour and 5-minute previews 10-second jump buttons for playback and fast forward						Access	functions Client monitoring	PathFinder [™] easy end-to-end remo	
,	•	1 5				Noticedia	software	C3 CMS, DW Mobile Plus mobile ap	
Event notifications via email, C3 [™] CMS and push notifications Compatible with DW [®] Spot [™] Monitoring module for Public View Monitors						Network functions Remote system control		Live monitoring, remote playback and file backup Remote system reboot, system management and PTZ control	
•	•		ring module f	or Public V	iew monitors	NETWORK	Firmware upgrade	FTP, USB and CMS over network	
	uts, 1 audio ou	•						Snapshot Notify: Programmable in	
8 sensor inputs, 2 relay outputs						Other function	Special features	Event notifications via email, text a Push notifications to mobile device	
Simple and	free DDNS se	rvice						Time synchronization to an NTP se	rver (pool.ntp.org)
Easy web-based client with multi-user access						Health check Backup device		Real-time system and network status monitoring Local backup by USB, network backup by CMS, watermark, AVI file	
Help menu on major functions						System recovery after power failure Auto-Reboot and journaling file system			
Auto and m	anual firmwar	e uparade	S			GENERAL Operating t	emperature/humidity	/ 32-113 °F (0~45 °C) / 10-90% RH	
Auto and manual firmware upgrades NDAA/TAA compliant						Certification		CE , FCC, KC, NDAA, TAA	
5 year limited warranty						Power requirements Power consumption		DC12V 48W, 4A	
J year minite	a warranty					Dimension	Dimension (W x D x H) 14.96" x 10.58" x 1.77" (x 45 mm)
						Warranty		5 year limited	

RTNER PROGRAM

E: 866.446.3595 States@digital-watchdog.com

Increase sales and profitability. Sign up and become a DW Channel Partner today!



: www.digital-watchdog.com



REV. 04/23



Available Models

- DW-VA1G48 8CH, no HDD.
- DW-VA1G482T 8CH, 2TB internal storage.
- DW-VA1G484T 8CH, 4TB internal storage.
- DW-VA1G486T 8CH, 6TB internal storage.
- DW-VA1G488T 8CH, 8TB internal storage.
- DW-VA1G4810T 8CH, 10TB internal storage.
- DW-VA1G4812T 8CH, 12TB internal storage.
- DW-VA1G4816T 8CH, 16TB internal storage.
- DW-VA1G4820T 8CH, 20TB internal storage.
- DW-VA1G4832T 8CH, 32TB internal storage.

Accessories (optional)



DW-G419RE 19" rack mount ears



Increase sales and profitability. Sign up and become a DW Channel Partner today!





